



NGF-TB1CLU7 | 1447210

Next Generation Frame (NGF) Fiber Termination Block, 96 SC/UPC, singlemode, left oriented, upward cable exit, putty white

Body Features

Cable Exit	Up
Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	96
Front Connector Type	SC/UPC
Block Capacity	96
Configuration	Adapters only

Dimensions

Depth	434.340 mm 17.100 in
Height	330.200 mm 13.000 in
Width	153.416 mm 6.040 in

Operation/Application

Environment	Central Office
For Use With	NGF Frames

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	EMEA Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Fiber Termination Block
System	NGF
Optical Mode	Singlemode
Orientation	Left

NGF-TB1CLU7 | 1447210

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant