



NGF-TB2MRU2 | 1389305

Next Generation Frame (NGF) Fiber Termination Block, 144 FC/UPC, singlemode, right oriented, upward cable exit, putty white

Body Features

Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	144
Front Connector Type	FC/UPC
Configuration	Adapters only

Dimensions

Depth	434.340 mm		17.100 in
Height	239.268 mm		9.420 in
Width	153.416 mm		6.040 in

Operation/Application

For Use With	NGF Frames
--------------	------------

Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

Product Availability

Region	EMEA		Latin America		North America
--------	------	--	---------------	--	---------------

Product Type Features

Product Type	Fiber Termination Block
System	NGF
Optical Mode	Singlemode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant