



NGF-TB4MLDK | 1450939

Next Generation Frame (NGF) Fiber Termination Block, 144 LC/UPC, singlemode, left oriented, downward cable exit, putty white

Body Features

Cable Exit	Down
Chassis Color	Putty white
Finish	Powder coated

Configuration Features

Number of Ports	144
Front Connector Type	LC/UPC
Block Capacity	144
Configuration	Adapters only

Dimensions

Depth	434.340 mm		17.100 in
Height	330.200 mm		13.000 in
Width	153.416 mm		6.040 in

Operation/Application

Environment	Central Office
For Use With	NGF Frames

Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

Product Availability

Region	EMEA		Latin America		North America
--------	------	--	---------------	--	---------------

Product Type Features

Product Type	Fiber Termination Block
System	NGF
Optical Mode	Singlemode
Orientation	Left

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant