



NGFB-TB4QLUK0BRO25 | 320000102717

Next Generation Frame (NGF) Fiber Termination Block with IFC Cable, singlemode, 192 LC/UPC to Stub tail, left oriented, upward cable exit, black, 25 m

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	192
Front Connector Type	LC/UPC
Configuration	Pre-terminated
Rear/Far End Connector Type	Stub tail

Dimensions

Cable Length	25.00 m 82.02 ft
--------------	--------------------

Operation/Application

For Use With	NGF Frames
--------------	------------

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	EMEA Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Fiber Termination Block with IFC cable
System	NGF
Included Cable	IFC cable
Optical Mode	Singlemode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant