

TFP-24MPRSQ5 | 1422163

TFP Fiber Optic Plug-and-Play 24-Fiber Cassettes, 12 LC/UPC singlemode adapters, angle right

Product Classification

Portfolio	NETCONNECT®
Product Series	TFP
Product Type	Fiber cassette
Regional Availability	Asia Latin America North America

Body Features

Color	Black
-------	-------

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	24
Port Capacity	24
Port Color	Beige
Port Style	Duplex
Rear/Far End Connector Type	MPO

Packaging Features

Packaging Method	Bag/Carton
Packaging Quantity	1

Product Type Features

Fiber Type	OM1
Optical Mode	Singlemode
Orientation	Angle Right

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant