

TFP-2TT00-000B | 1472965

TFP Fiber Termination/Splice Panel, unloaded, termination only rack/cabinet mount panel, 2 RU, 19 in, black, T-handle latch close

Product Classification

Portfolio	NETCONNECT®
Product Series	TFP
Product Type	Fiber termination panel
Regional Availability	Asia Latin America North America

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	0
Configuration	Unloaded

Dimensions

Depth	399.29 mm 15.72 in
Height	88.90 mm 3.50 in
Width	482.60 mm 19.00 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Type Features

Rack Units	2.0
Lock Type	No Locks

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant