

TFP-5TT00-000B | 1472840

**TFP Fiber Termination/Splice Panel, unloaded, termination only rack/cabinet mount panel, 5 RU, 19 in, black, T-handle latch close**

## Body Features

Chassis Color	Black
Finish	Powder coated

## Configuration Features

Access	Rear
Number of Ports	0
Configuration	Unloaded

## Dimensions

Depth	399.288 mm		15.720 in
Height	222.250 mm		8.750 in
Width	482.600 mm		19.000 in

## Packaging Features

Includes	Installation Instruction		Mounting hardware
Packaging Method	Box/Carton		
Packaging Quantity	1		

## Product Availability

Region	Asia		Latin America		North America
--------	------	--	---------------	--	---------------

## Product Type Features

Product Type	Fiber Termination Panel
System	TFP
Rack Units	5.0
Lock Type	No Locks

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant