

TMRJ-1SUPB-SS012M | 1-2111368-2

MRJ21™ High Speed Cable Assembly, MRJ21 to MRJ21, 180°–180°, 1GbE, 24-pair, CMR, 12 m, blue

Body Features

Cable Color	Blue
Cable Exit Type	Straight to straight
Shield Material	Carbon steel

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	24-pair
Number of Power Positions	0

Dimensions

Length	12.00 m 39.37 ft
Overall Outside Cable Diameter	0.460 mm 0.018 in
Wire Size (CMA)	.205 mm ² 24 AWG

Industry Standards

Approved Standards	cULus
Flammability Rating	CMP

Mechanical Attachment

Jackscrew	With
-----------	------

Operation/Application

Halogen Free	No
--------------	----

Product Availability

Region	Latin America North America
--------	-------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT MRJ21™
Assembly Type	Plug to Plug
Connector Type (End A)	MRJ21 Plug
Connector Type (End B)	MRJ21 Plug
Performance Category	1Gb Ethernet
Cable Assembly Category	High Speed
Latching Style	Jackscrews
Shielded	Yes

Signal Characteristics

TMRJ-1SUPB-SS012M | 1-2111368-2

Data Rate 1.00 Gb/s

Usage Conditions

Operating Temperature Range -10 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant