



TMRJ-1SURG-SS017M | 1-2111366-7

**MRJ21™ High Speed Cable Assembly, MRJ21 to MRJ21, 180°-180° 1GbE, 24-pair, CMP, 17 m, gray**

## Body Features

Cable Color	Gray
Cable Exit Type	Straight to straight
Shield Material	Carbon steel

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	24-pair
Number of Power Positions	0

## Dimensions

Length	17.00 m   55.77 ft
Overall Outside Cable Diameter	0.510 mm   0.020 in
Wire Size (CMA)	.205 mm <sup>2</sup>   24 AWG

## Industry Standards

Approved Standards	cULus
Flammability Rating	CMR

## Mechanical Attachment

Jackscrew	With
-----------	------

## Operation/Application

Halogen Free	No
--------------	----

## Product Availability

Region	Latin America   North America
--------	-------------------------------

## Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT   MRJ21™
Assembly Type	Plug to Plug
Connector Type (End A)	MRJ21 Plug
Connector Type (End B)	MRJ21 Plug
Performance Category	1Gb Ethernet

TMRJ-1SURG-SS017M | 1-2111366-7

Cable Assembly Category	High Speed
Latching Style	Jackscrews
Shielded	Yes

## Signal Characteristics

Data Rate	1.00 Gb/s
-----------	-----------

## Usage Conditions

Operating Temperature Range	-10 – 60 °C
-----------------------------	-------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant