

TMRJ-XSSRVV-SS011M | 1-2111521-1

**MRJ21™ Patch Cord, RJ45 modular plug to RJ45 modular plug, 10 Gb/s, CMR sheath, 11 m, white**

## Product Classification

Portfolio	NETCONNECT®
Brand	MRJ21™
Product Series	MRJ21
Product Type	Copper trunk cable assembly
Regional Availability	Latin America   North America

## Body Features

Cable Color	White
Cable Exit Type	Straight to straight
Shield Material	Carbon steel

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	16-pair
Number of Power Positions	0

## Dimensions

Length	11.00 m   36.09 ft
Wire Size (CMA)	.129 mm²   26 AWG

## Industry Standards

Flammability Rating	CMR
---------------------	-----

## Mechanical Attachment

Jackscrew	With
-----------	------

## Operation/Application

Halogen Free	No
--------------	----

## Product Type Features

Assembly Type	Plug to Plug
Connector Type (End A)	MRJ21 Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	10Gb Ethernet
Cable Assembly Category	High Speed
Latching Style	Jackscrews
Shielded	Yes

## Signal Characteristics

# Product Specifications



---

TMRJ-XSSRW-SS011M | 1-2111521-1

Data Rate 10.00 Gb/s

## Usage Conditions

---

Operating Temperature Range -10 – 60 °C

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Not Compliant