

TP6TBOGN15 | 1346982

**Ultim8 Category 6 Termination Block Patch Cords, green, 15 ft**

## Body Features

Cable Color	Green
Shield Style	UTP
Conductor Material	Stranded tinned copper
Conductor Type	Stranded

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0
Wiring Pattern	T568A

## Dimensions

Length	4.57 m   15.00 ft
Wire Size (CMA)	.205 mm <sup>2</sup>   24 AWG

## Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

## Operation/Application

Halogen Free	No
--------------	----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia   Latin America   North America
--------	--------------------------------------

## Product Type Features

Product Type	Patch Cord
System	TrueNet
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	Ultim8
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	No

## Usage Conditions

Operating Temperature Range	-10 – 60 °C
-----------------------------	-------------

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant