

TP6TBOWT10 | 1340399

Ultim8 Category 6 Termination Block Patch Cords, white, 10 ft

Body Features

Cable Color	White
Shield Style	UTP
Conductor Material	Stranded tinned copper
Conductor Type	Stranded

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0
Wiring Pattern	T568A

Dimensions

Length	3.05 m 10.00 ft
Wire Size (CMA)	.205 mm ² 24 AWG

Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

Operation/Application

Halogen Free	No
--------------	----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Patch Cord
System	TrueNet
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	Ultim8
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	No

Usage Conditions

Operating Temperature Range	-10 – 60 °C
-----------------------------	-------------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant