

VI-24-PTY | 1444443
Standard BNC Bulkhead Panel, 2 RU, 2 x 12, putty white

Product Classification

Product Type	Copper patch panel
Regional Availability	North America

Body Features

Color	Putty white
-------	-------------

Configuration Features

Port Capacity	24
Port Configuration	2 x 12
Front Connector Type	BNC
Preloaded	Yes

Dimensions

Rack Width	482.60 mm 19.00 in
------------	----------------------

Electrical Characteristics

Impedance	75 Ohms
-----------	---------

Mechanical Attachment

Mounting Style	Rack-Mount
----------------	------------

Product Type Features

Panel Type	Bulkhead
Rack Units	2.0
Product Category	Broadcast Modular System
Product Line	Broadcast
Size	Standard

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant