SIEMENS

Data sheet	US2:P1A30MC250CT
	Siemens Low Voltage RP1 Unassembled Lighting Panel. Dimensions (H x W x D) IN: 38.0 x 20.0 x 5.75. 1-Phase 3-Wire allows 30 circuits user selects Main Device (Lug/Breaker). Rated 120/240V (250A). Special features: tin-plated copper main bus, subfeed space included
Phase number	1
Suitability for operation	Lighting Loads/ Branch Circuit Loads
Model	
product brandname	SIEMENS
Product type designation	UPB interiors
Mechanical Design	
Material of the enclosure	Copper BUS
General product approval	
Certificate of suitability	PB1/UL67
last modified:	08/20/2017