



KRAMER

VS-211H2

2x1 4K60 4:4:4 HDCP 2.2 HDMI 2.0

Automatic Standby Switcher

| HDMI | HDCP Compliant | 4K/60 UHD (4:2:0)

| 4K/60 UHD (4:4:4)



The VS-211H2 is a high-performance automatic switcher for 4K@60Hz (4:4:4) HDCP 2.2 HDMI 2.0 video signals. Offering priority and last-connected switching options, it automatically switches according to the selected switching scheme based on active video signal detection

FEATURES

Max. Data Rate - 17.82Gbps (5.94Gbps per data channel)

Max. Resolution - 4K@60Hz (4:4:4)

Kramer Equalization and re-Klocking Technology

HDTV Compatible

HDMI 2.0 & HDCP 2.2 Compliant

3D Pass-Through



KRAMER

TECHNICAL SPECIFICATIONS

INPUTS:	2 HDMI connectors
OUTPUTS:	1 HDMI connector
MAX. DATA RATE:	17.82GBPS (5.94Gbps per graphic channel)
MAX. RESOLUTION	4K@60 UHD (4:4:4)
COMPLIANCE WITH HDMI STANDARD:	HDCP and HDMI
CONTROLS:	Status/priority DIP-switches, contact closure remote control
REGULATORY CERTIFICATION:	EMC EN 55032;IEC 60950-1(ed.2);IEC 60950-1(ed.2)am1;IEC 60950-1(ed.2)am2
OPERATING TEMPERATURE:	0° to +40°C (32° to 104°F)
STORAGE TEMPERATURE:	-40° to +70°C (-40° to 158°F)
HUMIDITY:	10% to 90%, RHL non-condensing
POWER CONSUMPTION:	5V DC, 400mA
PRODUCT DIMENSION:	12.00cm x 7.15cm x 2.44cm (4.72" x 2.81" x 0.96") W, D, H
PRODUCT WEIGHT:	0.2kg (0.4lbs) approx
SHIPPING DIMENSION:	15.70cm x 12.00cm x 8.70cm (6.18" x 4.72" x 3.43") W, D, H
SHIPPING WEIGHT:	0.6kg (1.4lbs) approx
INCLUDED ACCESSORIES:	Power supply 5.2V DC/4A desktop
OPTIONS:	RK-3T 19" rack adapter

