



# 16-Port Gigabit PoE+ Switch

# TPE-TG160g (v1.1R)

- 16 x Gigabit PoE+ ports
- 246 W PoE budget
- 32 Gbps switching capacity
- Sturdy metal switch
- Rack mount brackets included
- Limited Lifetime Warranty

TRENDnet's 16-Port Gigabit PoE+ Switch, model TPE-TG160g, offers 16 x Gigabit PoE+ ports, a 32 Gbps switching capacity, and a PoE power budget of 246 Watts. This rugged metal switch comes with a rack mount kit.

# TRENDIET



# **PoE Camera Flexibility**

The switch recognizes non-PoE, PoE (15.4 W), and PoE+ (30 W) cameras (or other PoE devices) and supplies the required amount of power automatically.



# **Full PoE Power**

The large 246 Watt PoE power budget supplies full PoE power to every port, thereby maximizing the number of allowable connected PoE devices.



# **Gigabit Networking**

All Gigabit ports produce a 32 Gbps switching capacity and support Jumbo Frames up to 10 KB.

# **Networking Solution**







# PoE+

Supplies up to 30 Watts of power per port with a 246 Watt PoE budget



# **Ports**

16 x Gigabit PoE+ ports



# **Switching Capacity**

32 Gbps switching capacity



# **Jumbo Frame**

Sends Jumbo Frames (up to 10 KB) for increased performance



# **Energy Savings**

Embedded GREENnet technology reduces power consumption



# **Rack Mountable**

Rack mountable metal endosure with included mounting kit



# **LED Indicators**

LED indicators convey port status



# **Specifications**

#### Standards

- IEEE 802.1p
- IEEE 802.3
- IEEE 802.3u
- IEEE 802.3x
- IEEE 802.3ab
- IEEE 802.3af (15.4 Watts / port)
- IEEE 802.3at (30 Watts / port)
- IEEE 802.3az

#### **Device Interface**

- 16 x Gigabit PoE/PoE+ ports
- LED indicators

## **Data Transfer Rate**

- Ethernet: 10 Mbps (half duplex), 20 Mbps (full duplex)
- Fast Ethernet: 100 Mbps (half duplex), 200 Mbps (full duplex)
- Gigabit: 2,000 Mbps (full duplex)

#### **Performance**

- Data RAM Buffer: 512 KB
- Switch Fabric: 32 Gbps
- MAC Address Table: 8 K entries
  Forwarding rate: 23.8 Mpps (64-byte packet size)
- Jumbo Frame: 10 KB

#### Power

- Input: 110-240 V AC, 50/60 Hz, 54 V / 4.82 A; 12 V / 1.67 A
- Consumption: 36 Watts (Max. without PD)

#### PoE

- PoE budget: 246 Watts
- Pin 3,6 for power+ and pin 1,2 for power- (mode A)
- Over current protection
- Short circuit protection

## **Operating Temperature**

•0-40°C (32-104°F)

# **Operating Humidity**

• Max. 90% non-condensing

#### Dimensions

• 440 x 210 x 44 mm (17.3 x 8.3 x 1.7 in.)

## Weight

• 3 kg (6.8 lbs.)

# Certifications

- CE
- FCC

#### Warranty

• Limited Lifetime Warranty

# **Package Contents**

- TPE-TG160g
- Quick Installation Guide
- Rack mount kit
- Power cord

TRENDnet offers a limited lifetime warranty for all of its metal-enclosed network switches that have been purchased in the United States/Canada on or after 1/1/2015. Cooling fan and internal power supply carry a one-year warranty.

