

Wireless HDMI Extender 1080p with IR Control, 50 m (165 ft.)

MODEL NUMBER: **B126-1A1-WHD1**



Description

The B126-1A1-WHD1 Wireless HDMI Extender 1080p is an all-in-one wireless solution for extending an HDMI audio/video signal up to 50 meters (165 feet). No costly, bulky cabling infrastructure is needed, making the extender kit ideal for home theaters, office workstations, digital signage and trade show presentations where connecting long video cables would be a burden.

Merely connect HDMI cables (such as Tripp Lite's P568-Series) and the included IR cables to the transmitter and receiver units, then connect the included external power supplies to both units and a compatible AC power source. IR control functionality lets you access the HDMI source device remotely, meaning you can stand near the display device 50 meters away and activate play, pause, fast forward and other functions on the source's remote.

The B126-1A1-WHD1 supports high-definition video resolutions up to 1920 x 1080 (1080p) at 60 Hz. It's compatible with HDMI 1.3 and HDCP 1.2, and supports 24-bit Deep Color (8 bits per channel) and stereo audio, as well as 300 MHz/3.4 Gbps per channel bandwidth (10.2 Gbps total). AES 128 encryption protects your wireless transmissions. LEDs indicate the units are receiving power, transmitting data and connected to a wireless signal.

With no busy cabling infrastructure to clutter your application, you're free to move your source and display devices where needed. The plug-and-play B126-1A1-WHD1 needs no additional software or drivers to operate. International plug adapters for North America, Europe, the United Kingdom and Australia are included with the power supplies.

Features

Wirelessly Extends an HDMI Audio/Video Signal Up to 50 m (165 ft.)

- Easy no-fuss, no-mess setup with no costly cabling infrastructure
- Ideal for homes, offices, digital signage applications, trade shows and anywhere else where connecting long video cables is impractical

Highlights

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- IR control for accessing HDMI source device remotely
- Compatible with HDMI 1.3 and HDCP 1.2
- Supports 24-bit Deep Color and stereo audio
- Easy no-fuss setup with no cabling infrastructure

System Requirements

- Source device with HDMI output (Blu-ray™ player, cable box, etc.)
- Display device with HDMI input (HDTV, projector, monitor)

Package Includes

- Transmitter unit
- Receiver unit
- IR-In cable
- IR-Out cable
- (2) External power supplies (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 3A)
- (2) Sets of international plug adapters (North America, Europe, U.K., Australia)
- Mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Enhanced Technical Features

- Supports video resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- Extends IR control signals that control an HDMI source from the remote display
- Compatible with HDMI 1.3 and HDCP 1.2
- Supports 24-bit Deep Color (8 bits per channel) and stereo audio
- Supports 300 MHz/3.4 Gbps per channel bandwidth (10.2 Gbps total)
- AES 128 encryption protects transmissions
- Uses a 5GHz wireless frequency
- LEDs indicate power, data transmission and connection status

Plug-and-Play Functionality

- No software or drivers required
- Mounting hardware included for installing transmitter and receiver units in desired location

Specifications

| OVERVIEW | |
|-------------------------------|---|
| AC Adapter | Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft. |
| PHYSICAL | |
| Included Mounting Accessories | Yes |
| Color | Black |
| ENVIRONMENTAL | |
| Operating Temperature Range | 0 to 40 C (32 to 104 F) |
| Storage Temperature Range | -20 to 60 C (-4 to 140 F) |
| Relative Humidity | 20 to 90% |
| COMMUNICATIONS | |
| Max 1024 x 768 Range (ft) | 200 |
| Max 480P Range (ft) | 200 |
| Max 1440 x 900 Range (ft) | 200 |
| Max 1080i Range (ft) | 200 |
| Max 1080P Range (ft) | 150 |
| Max 480i Range (ft) | 200 |
| Max 640 x 480 Range (ft) | 200 |
| Max 800 x 600 Range (ft) | 200 |
| Max 1600 x 1200 Range (ft) | 200 |
| Max 720P Range (ft) | 200 |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| CONNECTIONS | |
|-------------------------------------|-------------------------|
| Ports | 1 |
| Side A - Connector 1 | HDMI (FEMALE) |
| Side B - Connector 1 | HDMI (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| 10/100 Ethernet Extension Support | No |
| CERTIFICATIONS | |
| Certifications | Tested to |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>