

## Heavy-Duty Tilt Wall Mount for 37" to 80" TVs and Monitors, Flat or Curved Screens, UL Certified

MODEL NUMBER: DWT3780XUL



### Description

The VESA-compliant DWT3780XUL Heavy-Duty Tilt Wall Mount allows you to mount your flat-panel or curved-screen television, monitor or other display on the wall. Recommended for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most displays from 37 to 80 inches.

A -10° to 0° tilt capability minimizes glare and provides comfortable viewing from multiple angles. Adjusting the tilt angle is simple using the easy-grip twin knobs located on the wall plate.

The mount is concealed behind the display to give a sleek, professional appearance. An open back enables easy access to cabling. Built-in bubble level allows accurate wall plate leveling. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 165 pounds. Mounting hardware included.

Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm and 800 x 400 mm.

This mount has been tested in accordance with UL Standard 2442.

### Features

#### Mounts Your TV or Monitor to the Wall

- Fits most flat-panel or curved-screen televisions, monitors and other displays from 37 to 80 in.
- Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants
- Mounts out of sight behind display for sleek, professional appearance
- Mounting hardware included

#### Convenient Angle Adjustment

- -10° to 0° tilt capability provides comfortable viewing from multiple angles

### Highlights

- Fits most flat-panel or curved-screen displays from 37 to 80 in.
- Open architecture enables easy access to cabling
- -10° to 0° tilt capability for comfortable viewing
- Tested in accordance with UL Standard 2442
- Supports up to 165 lb.

### Package Includes

- Wall plate
- (2) Adapter brackets
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 30 screws
- (4) M8 x 50 screws
- (4) Washers
- (8) Small spacers
- (8) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



- Improves viewing angles in applications where audience is below the display
- Easy-grip knobs allow simple adjustment of tilt angle

#### Durable Metal Construction

- Supports up to 165 lb.
- Open architecture enables easy access to cabling
- Built-in bubble level for accurate display leveling
- Scratch-resistant powder-coated finish
- Tested in accordance with UL Standard 2442

#### VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm and 800 x 400 mm

## Specifications

PHYSICAL	
Mounting Location	Wall
Unit Dimensions (hwd / in.)	33.46 x 1.81 x 7.99
Unit Dimensions (hwd / cm)	85.1 x 4.6 x 20.3
Unit Weight (lbs.)	7.9
Unit Weight (kg)	3.58
Material of Construction	Steel
Color	Black
Screen Size Compatibility (in.)	37 - 70
Screen Size Compatibility (cm)	94.1 - 178.0
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400
Motion	Tilt
Distance from Wall (in.)	1.81
Distance from Wall (cm)	5
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Distance from Wall (mm)	46
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>