

MCH 7

Sennheiser MCH 7 Multi-USB Power Source for CH 10 Headset Charger

Sennheiser MCH 7 is a multi-USB power source that can power 7 Sennheiser CH 10 headset chargers simultaneously.

Benefits and Features

- Charging time: 3 hours
- Sennheiser MCH 7 multi-USB power source works with the following Sennheiser power supplies:
 - 94707 UNI PS EU 01
 - 92892 UNI PS UK 01
 - 92893 UNI PS US 01
 - 520334 UNI PS AUS 01

Specifications

Product name	MCH 7
Art. No.	504348
EAN No.	40 44155 05082 0
UPC No.	6 15104 18030 7
General Data	
Number of USB sockets	7
Weight	50 g / 1.76 oz
Technical data	
Input voltage	6 VDC, nominal (5.5 V – 9.0 V)
Input current	125 mA required per CH 10
Output voltage	5 V (±0.25 V)
Output current	100 mA per USB socket
Packaging	
Single packaging weight	72 g / 2.54 oz
Dimension of product packaging (W x H x D)	150 x 200 x 20 mm / 5.90 x 7.87 x 0.78 in
Dimension of inner master carton (W x H x D)	150 x 200 x 150 mm / 5.90 x 7.87 x 5.90 in
Dimension of outer master carton (W x H x D)	430 x 330 x 360 mm / 16.93 x 12.99 x 14.17 in
Units in inner master carton	14
Units in outer master carton	8 inner cartons with 14 units = 112 units / master carton
Outer master carton weight incl. products	9.9 kg / 21.82 lb
Inner master carton weight incl. products	1.2 kg / 2.65 lb
Warranty	2 years