

OUTSOURCE™

POWER OVER ETHERNET MIDSPAN INJECTOR



Compact, midspan injectors that deliver reliable POE for IP cameras and devices

Delivers enhanced POE to all 802.3af/802.3at POE and POE Plus devices. OUTSOURCE & OUTSOURCE Plus automatically detect compatible devices.

Delivers reliable remote power to IP cameras including PTZ devices

Designed for straightforward installation for high power devices

Safety assured as POE is only enabled to compliant equipment

Compact, wall-mountable unit

Integrated overload protection

Sealed, fanless design for reliability



TECHNICAL SPECIFICATION

OUTSOURCE™ / PLUS™

POWER									
Input Voltage	90 to 264V AC, 47 to 63Hz								
Maximum current	0.55A								
FORWARDED POE POWER									
OUTSOURCE	19.6 watts (Output voltage 56V)								
OUTSOURCE Plus	30 watts (Output voltage 56V)								
Overload and short-circuit protection POE output on data pairs (1 & 2, 3 & 6)									
POE STANDARDS									
OUTSOURCE	IEEE 802.3af POE								
OUTSOURCE Plus	IEEE 802.3at POE								
ETHERNET INTERFACE									
RJ45 Data IN port RJ45 Data & POE OUT port 10/100/1000 Base-T compatible									
LEDS									
Status indicators	<table border="0"> <tr> <td>Solid Green LED</td> <td>POE load detected, POE output ON</td> </tr> <tr> <td>Blinking Green LED</td> <td>Power on, no POE load</td> </tr> <tr> <td>Blinking Red/Green LED</td> <td>Invalid load connected</td> </tr> <tr> <td>Blinking Red LED</td> <td>Fault condition</td> </tr> </table>	Solid Green LED	POE load detected, POE output ON	Blinking Green LED	Power on, no POE load	Blinking Red/Green LED	Invalid load connected	Blinking Red LED	Fault condition
Solid Green LED	POE load detected, POE output ON								
Blinking Green LED	Power on, no POE load								
Blinking Red/Green LED	Invalid load connected								
Blinking Red LED	Fault condition								
PHYSICAL / ENVIRONMENTAL									
Dimensions	L 163mm (inc mounting holes) W 65mm H 36mm								
Weight	200g (7.06oz)								
Mounting	Integral wall-mount lugs								
Operating temperature	0°C to +40°C (32°F to 104°F)								
Relative humidity	5% to 90% non-condensing								
Compliance	CE, FCC, RoHS								
PRODUCT CODES									
VOR-OS	OUTSOURCE POE Injector								
VOR-OSP	OUTSOURCE Plus POE Plus Injector								



OUTSOURCE PLUS



OUTSOURCE



veracity

Americas & Asia Sales :

Veracity USA Inc.
65 Harristown Road
Glen Rock
NJ 07452

USA
Tel: 1-800-679-1590
Fax: 1-800-679-0714
www.veracityglobal.com
sales@veracityusa.com

EMEA Sales :

Veracity UK Ltd
Prestwick International Aerospace Park
4 Dow Road
Prestwick
KA9 2TU
UK

Tel +44 (0) 1292 264967
Fax +44 (0) 845 528 1081
www.veracityglobal.com
sales@veracityuk.com