

OUTBREAK™

POWER OVER ETHERNET SPLITTER



POE splitter for delivering power via POE to non-POE network devices

Delivers 5V or 12V DC to non-POE devices from a POE network source by splitting data and power.

Simple POE splitter delivering clean power to non-POE devices

Fully IEEE 802.3af compliant and gigabit compatible

Steps down POE voltage (48V) to 5V or 12V DC

Compact unit with integral wall mount lugs

Ideal for non-POE wireless access points, IP phones, IP cameras



TECHNICAL SPECIFICATION] OUTBREAK™

POWER	
Input voltage	36V to 56V DC, receiving power on either data or spare pairs
Input current	0.6A at 36V maximum load
OUTPUT POWER	
OUTBREAK 5	12.5 watts at 5V DC
OUTBREAK 12	12-14 watts at 12V DC
	Output with short-circuit protection
DC Output connector	Barrel connector 9mm x 2.5mm x 5.5mm, centre positive
POE STANDARDS	
	IEEE 802.3af POE
ETHERNET INTERFACE	
	RJ45 Data and POE IN port
	RJ45 Data OUT port
	10/100/1000 Base-T compatible
LEDS	
Status indicator	Green LED ON - Output OK
PHYSICAL/ENVIRONMENTAL	
Dimensions	L 100mm (excluding flying lead) W 56mm H 28mm
Weight	200g (7.0oz)
Mounting	Integral wall-mount lugs
Operating temperature	0°C to +40°C (32°F to 104°F)
Relative humidity	5% to 90% non-condensing
Compliance	CE, FCC, RoHS
PRODUCT CODES	
	VOR-OB5 OUTBREAK 5V 5V POE Splitter
	VOR-OB12 OUTBREAK 12V 12V POE Splitter



OUTBREAK 12V

OUTBREAK 5V



veracity

Americas & Asia Sales :

Veracity USA Inc.
65 Harristown Road
Glen Rock
NJ 07452

USA
Tel: 1-800-679-1590
Fax: 1-800-679-0714
www.veracityglobal.com
sales@veracityusa.com

EMEA Sales :

Veracity UK Ltd
Prestwick International Aerospace Park
4 Dow Road
Prestwick
KA9 2TU
UK

Tel +44 (0) 1292 264967
Fax +44 (0) 845 528 1081
www.veracityglobal.com
sales@veracityuk.com