

## Data Center Equipment ID (B-422, B-483, B-595)

Durable materials with permanent adhesive suited to adhere to rough, highly textured or powder coated surfaces. Available in a variety of sizes and colors for marking racks, bays, frames, slots, and other voice/data hardware.




Figure 29



Figure 33



Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Material Notes	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
<b>B-422 – Gloss Polyester</b>									
BMP41, 51, 53	Fig. 29	M-7-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	0.500 (12.70)	0.500 (12.70)	280
BMP41, 51, 53	Fig. 33	MC-500-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	0.500 (12.7)	25 ft (7.6 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 29	M-47-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	1.000 (25.40)	0.500 (12.70)	360
BMP41, 51, 53	Fig. 29	M-49-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	1.000 (25.40)	1.000 (25.40)	200
BMP41, 51, 53	Fig. 29	MC1-1000-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	1.000 (25.40)	25 ft (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 29	M-89-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	1.500 (38.10)	0.500 (12.70)	360
BMP41, 51, 53	Fig. 29	M-90-422	B-422	Gloss Polyester	BK on WT	For smooth or textured surfaces	1.500 (38.10)	0.750 (19.05)	200
<b>B-483 – Ultra Aggressive Polyester</b>									
BMP41, 51, 53	Fig. 29	M-47-483	B-483	Polyester	BK on WT	For smooth or textured surfaces	1.000 (25.40)	0.500 (12.70)	360
BMP41, 51, 53	Fig. 29	M-61-483	B-483	Polyester	BK on WT	For smooth or textured surfaces	2.000 (50.80)	0.500 (12.70)	80
BMP41, 51, 53	Fig. 29	M-60-483	B-483	Polyester	BK on WT	For smooth or textured surfaces	2.000 (50.80)	1.000 (25.40)	80
<b>B-595 – Indoor / Outdoor Vinyl Tape*</b>									
BMP41, 51, 53	Fig. 33	MC-500-595-WT-BK	B-595	Vinyl	BK on WT	In/Outdoor Vinyl for dark surfaces	0.500 (12.70)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-WT-BK	B-595	Vinyl	BK on WT	In/Outdoor Vinyl for dark surfaces	0.750 (19.05)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-WT-BK	B-595	Vinyl	BK on WT	In/Outdoor Vinyl for dark surfaces	1.000 (25.40)	20 ft (6.09 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-WT-BK	B-595	Vinyl	BK on WT	In/Outdoor Vinyl for dark surfaces	1.500 (38.10)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-CL-WT	B-595	Vinyl	WT on CL	In/Outdoor Vinyl for dark surfaces	0.500 (12.70)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-CL-WT	B-595	Vinyl	WT on CL	In/Outdoor Vinyl for dark surfaces	0.750 (19.05)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-CL-WT	B-595	Vinyl	WT on CL	In/Outdoor Vinyl for dark surfaces	1.000 (25.40)	20 ft (6.09 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-CL-WT	B-595	Vinyl	WT on CL	In/Outdoor Vinyl for dark surfaces	1.500 (38.10)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-500-595-YL-BK	B-595	Vinyl	BK on YL	In/Outdoor Vinyl for dark surfaces	0.500 (12.70)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-YL-BK	B-595	Vinyl	BK on YL	In/Outdoor Vinyl for dark surfaces	0.750 (19.05)	20 ft (6.09 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-YL-BK	B-595	Vinyl	BK on YL	In/Outdoor Vinyl for dark surfaces	1.000 (25.40)	20 ft (6.09 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-YL-BK	B-595	Vinyl	BK on YL	In/Outdoor Vinyl for dark surfaces	1.500 (38.10)	20 ft (6.09 m)	1 roll (cont.)

\* For additional vinyl label colors, refer to the B-595 Indoor/Outdoor Grade Facility and Safety Labels on page 18.

## Labels for Bin, Storage, Lean 5S and General Industrial ID (B-483, B-499, B-595)

Choose from several materials with aggressive adhesives for use in commercial/industrial applications, including low surface energy and textured surfaces.




Figure 29



Figure 33



Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/Roll
<b>B-483 – Ultra Aggressive Polyester</b>								
BMP41, 51, 53	Fig. 29	M-47-483	B-483	Polyester	BK on WT	1.000 (25.40)	0.500 (12.70)	360
BMP41, 51, 53	Fig. 29	M-60-483	B-483	Polyester	BK on WT	2.000 (50.80)	1.000 (25.40)	80
BMP41, 51, 53	Fig. 29	M-61-483	B-483	Polyester	BK on WT	2.000 (50.80)	0.500 (12.70)	80
<b>B-499 – Nylon Cloth</b>								
BMP41, 51, 53	Fig. 29	M-11-499	B-499	Nylon Cloth	BK on WT	0.750 (19.05)	0.500 (12.70)	220
BMP41, 51, 53	Fig. 29	M-84-499	B-499	Nylon Cloth	BK on WT	0.900 (22.86)	0.500 (12.70)	200
BMP51, 53	Fig. 29	M-132-499	B-499	Nylon Cloth	BK on WT	1.500 (38.10)	1.250 (31.75)	160
BMP41, 51, 53	Fig. 29	M-128-499	B-499	Nylon Cloth	BK on WT	1.900 (48.26)	1.000 (25.40)	100
<b>B-595 – Indoor / Outdoor Vinyl Tape*</b>								
BMP41, 51, 53	Fig. 33	MC-750-595-WT-BK	B-595	Vinyl	BK on WT	0.750 (19.10)	25 ft (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-WT-BK	B-595	Vinyl	BK on WT	1.000 (25.40)	25 ft (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-WT-BK	B-595	Vinyl	BK on WT	1.500 (38.10)	25 ft (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC-750-595-YL-BK	B-595	Vinyl	BK on YL	0.750 (19.10)	25 ft (7.62 m)	1 roll (cont.)
BMP41, 51, 53	Fig. 33	MC1-1000-595-YL-BK	B-595	Vinyl	BK on YL	1.000 (25.40)	25 ft (7.62 m)	1 roll (cont.)
BMP51, 53	Fig. 33	MC-1500-595-YL-BK	B-595	Vinyl	BK on YL	1.500 (38.10)	25 ft (7.62 m)	1 roll (cont.)

\* For additional vinyl label colors, refer to the B-595 Indoor/Outdoor Grade Facility and Safety Labels on page 18.