

Sample Collection & Processing Labels

BradyID.com/lab

Microcentrifuge & PCR Tubes Labels

Designed with ultra-thin material that prevents vials from jamming in centrifuges or racks, these labels withstand harsh temperatures and chemicals without falling off, fading or smearing.

- B-461 – Ultra-thin polyester label with clear overlamine tail that protects print and allows liquid levels to be visible.
- B-490 – White FreezerBondz™ label ideal for flat frozen surfaces. Adheres to frozen tube and vials when wrapped around itself by at least 1/8 inch.
- B-492 – FreezerBondz™ ultra-thin white polyester label for labeling of frosted/frozen or room temperature vials, tubes and canes. Superior chemical and abrasion resistance.
- B-499 – Permanent Adhesive - Thick white nylon cloth for easy handling and conformability.
- B-7425 – Economic white polypropylene label with moderate chemical resistance, ideal for labeling dry, room temperature specimen containers.




Figure 26




Figure 33

Sample Collection & Processing

Fits Printer Model(s)	Tube Size	Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Label Area C Inch (mm)	Labels Per Row	Labels per Roll	Rec. Ribbon
BMP21-Lab Printer Cartridges											
BMP21-LAB Printer	0.6 ml	Fig. 33	M21-250-430	B-430	BK on WT	0.250 (6.35)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-375-430	B-430	BK on WT	0.375 (9.5)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-375-461	B-461	BK on WT	0.375 (9.5)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-375-499	B-499	BK on WT	0.375 (9.5)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-375-7425	B-7425	BK on WT	0.375 (9.5)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
	1.0 - 8.0 ml	Fig. 33	M21-500-430	B-430	BK on WT	0.500 (12.7)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-500-461	B-461	BK on WT	0.500 (12.7)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-500-499	B-499	BK on WT	0.500 (12.7)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-500-7425	B-7425	BK on WT	0.500 (12.7)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-750-430	B-430	BK on WT	0.750 (19.1)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-750-461	B-461	BK on WT	0.750 (19.1)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-750-499	B-499	BK on WT	0.750 (19.1)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		Fig. 33	M21-750-7425	B-7425	BK on WT	0.750 (19.1)	21 ft (6.4 m)	-	1	1 roll (cont.)	-
		BMP51 Label Printer Cartridges									
BMP51 Printer	0.5 - 1.5 ml Top	Fig. 26	M-82-492	B-492	BK on WT	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499	B-499	BK on WT	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499	B-499	BK on WT	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-OR-BK	B-499	BK on OR	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-OR-BK	B-499	BK on OR	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-RD-BK	B-499	BK on RD	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-RD-BK	B-499	BK on RD	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-YL-BK	B-499	BK on YL	0.375 (9.5)	-	-	1	240	-
		Fig. 26	M-82-499-YL-BK	B-499	BK on YL	0.375 (9.5)	-	-	1	240	-

Microcentrifuge & PCR Tubes Labels continued on next page.