

AXIS M5525-E PTZ Network Camera

Indoor and outdoor PTZ with 10x zoom

AXIS M5525-E PTZ Network Camera is a compact pan-tilt-zoom camera with HDTV 1080p resolution, 10x optical zoom, and autofocus, enabling great video quality in both overview and detail. Day/night functionality and WDR – Forensic Capture ensures maintained image quality in low or mixed light, and scene profiles are included for automatic optimization. AXIS M5525-E is compatible with any Axis PTZ mount for outdoor installation, but can also be surface-mounted indoors. Protected against dust, rain, snow, and corrosion, the camera operates in temperatures from -20 °C to 50 °C (-4 °F to 122 °F). The microSD card slot enables local video storage.

- > [HDTV 1080p with 10x optical zoom](#)
- > [Continuous 360° for uninterrupted pan](#)
- > [WDR — Forensic Capture](#)
- > [Axis Zipstream technology](#)
- > [I/O ports and two-way audio](#)



AXIS M5525-E PTZ Network Camera

Camera		
Image sensor	1/2.8" progressive scan CMOS	
Lens	4.7–47 mm, F1.6–3.0 Horizontal field of view: 61.8°–6.7° Vertical field of view: 37.2°–3.8° Autofocus, auto-iris	
Day and night	Automatically removable infrared-cut filter	
Minimum illumination	Color: 0.45 lux at 30 IRE F1.6 B/W: 0.01 lux at 30 IRE F1.6 Color: 0.55 lux at 50 IRE F1.6 B/W: 0.01 lux at 50 IRE F1.6	
Shutter time	1/66500 s to 2 s	
Pan/Tilt/Zoom	Pan: 360° endless, 1.8°–150°/s Tilt: 90°, 1.8°–150°/s 10x optical zoom, 12x digital zoom, total 120x zoom Nadir flip, 100 preset positions, limited guard tour, control queue, on-screen directional indicator	
Video		
Video compression	H.264 (MPEG-4 Part 10/AVC) – Baseline, Main and High Profiles Motion JPEG	
Resolution	1920x1080 to 320x180	
Frame rate	Up to 25/30 fps with power line frequency 50/60 Hz	
Video streaming	Multiple, individually configurable streams in H.264 and Motion JPEG Axis Zipstream technology in H.264 Controllable frame rate and bandwidth VBR/MBR H.264	
Image settings	Saturation, brightness, sharpness, WDR – forensic capture, white balance, exposure mode, exposure zones, compression, text and image overlay, 20 individual 3D privacy masks, contrast, scene profiles, image freeze on PTZ, local contrast, max shutter, max gain, noise/motion priority, aperture lock, exposure level Rotation: 0°, 180°	
Audio		
Audio streaming	Two-way, full duplex	
Audio compression	AAC-LC 8/16/32 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz Configurable bit rate	
Audio input/output	External microphone input or line input, line output	
Network		
Security	Password protection, IP address filtering, HTTPS ^a encryption, IEEE 802.1X ^a network access control, Digest authentication, User access log, Centralized Certificate Management	
Supported protocols	IPv4/v6, HTTP, HTTPS ^a , SSL/TLS ^a , QoS Layer 3 DiffServ, FTP, SFTP, CIFS/SMB, SMTP, Bonjour, UPnP TM , SNMP v1/v2c/v3(MIB-II), DNS, DynDNS, NTP, RTSP, RTP, TCP, UDP, IGMP, RTCP, ICMP, DHCP, ARP, SOCKS, SSH	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX [®] and AXIS Camera Application Platform; specifications at www.axis.com AXIS Video Hosting System (AVHS) with One-Click Connection ONVIF Profile S and ONVIF Profile G, specification at www.onvif.org	
Analytics	Included AXIS Video Motion Detection, audio detection, Advanced Gatekeeper Supported AXIS Cross Line Detection, AXIS Guard Suite including AXIS Fence Guard, AXIS Motion Guard Support for AXIS Camera Application Platform enabling installation of third-party applications, see www.axis.com/acap	
Event triggers	Analytics, edge storage events Detectors: day/night mode, live stream accessed, audio detection Hardware: network, temperature Input Signal: digital input port, manual trigger, virtual inputs PTZ: error, moving, preset reached, ready Storage: disruption, recording System: system ready	
		Time: recurrence, use schedule
Event actions	Record video: SD card and network share Upload of images or video clips: FTP, SFTP, HTTP, HTTPS, network share, and email Pre- and post-alarm video or image buffering for recording or upload Notification: email, HTTP, HTTPS, TCP, and SNMP trap PTZ: PTZ preset, start/stop guard tour Overlay text, play audio clip, external output activation, WDR mode	
Data streaming	Event data	
Built-in installation aids	Pixel counter	
General		
Casing	IP66-, NEMA 4X- and IK09-rated Repaintable plastic casing, polycarbonate (PC) dome	
Sustainability	PVC free	
Memory	512 MB RAM, 256 MB Flash	
Power	Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3 Typical 6.6 W, max 12.95 W 20–28 V DC, typical 6.3 W, max 13 W (PoE midspan and power supply not included)	
Connectors	RJ45 10BASE-T/100BASE-TX PoE DC input terminal block I/O: 6-pin terminal block with push-in spring connection for four configurable inputs/outputs Audio: mic/line in, line out terminal block with push-in spring connection	
Storage	Support for microSD/SDHC/SDXC card (not included) Support for SD card encryption Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see www.axis.com	
Operating conditions	-20 °C to 50 °C (-4 °F to 122 °F) Humidity 15–100% RH (condensing)	
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)	
Approvals	EMC EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35 Safety IEC/EN/UL 62368-1, IEC/EN/UL 60950-22 Environment IEC 60068-2-27, IEC 60068-2-6, IEC/EN 60529 IP66, IEC/EN 62262 IK09	
Dimensions	Height: 132 mm (5.2 in) ø 165 mm (6.5 in)	
Weight	1.1 kg (2.4 lb) Recessed mount (plenum rated): 1.0 kg (2.2 lb)	
Included accessories	Conduit adapter 3/4", smoked dome, adapter bayonet Installation Guide, Windows decoder 1-user license	
Optional accessories	T91 Mounting Accessories, AXIS T94P01L Recessed Mount Kit	
Video management software	AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available on www.axis.com/support/downloads	
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese	
Warranty	Axis 3-year warranty and AXIS Extended Warranty option, see www.axis.com/warranty	
<p>a. This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (www.openssl.org), and cryptographic software written by Eric Young (ey@cryptsoft.com).</p>		
<p>Environmental responsibility: www.axis.com/environmental-responsibility</p>		