

Y Splitter Computer Power Extension Cord, 10A, 18AWG (IEC-320-C14 to 2x IEC-320-C13), 6-ft.

MODEL NUMBER: P004-006-2C13



Highlights

- Connect two devices to one power outlet
- UL Listed
- Plug type - C14 to 2 x C13
- 18AWG (0.824mm²), SJT, 10A, 100-250V

Package Includes

- P004-006-2C13 6-ft. AC Power Extension Splitter Cord (C14 to 2 x C13)

Description

Tripp Lite's P004-006-2C13, 6ft Universal AC Power Extension Cord Splitter, allows you to connect two devices with C14 connections, such as computers, to one power outlet. Cuts down on cabling, as well as frees up space on UPS's, Surge Protectors, etc. The total length of the cord is 6-ft, and it is split equally into 3-ft. sides from the center.

Features

- Power two computers or other device from one outlet
- UL Listed
- Plug type - C14 to 2 x IEC-320-C13 (Device)
- 18AWG (0.824mm²), SJT, 10A, 100-250V
- 6-ft. overall length, split equally into 3-ft. sides from the center

Specifications

INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(2) IEC-320-C13



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>