

## Universal Computer Power Cord, 10A, 18AWG (NEMA 5-15P to IEC-320-C13 with Red Plugs), 4-ft.

MODEL NUMBER: P006-004-RD



### Highlights

- Red color-coded 5-15P and C13 connectors
- 18AWG, 10A, 125V
- UL Listed

### Package Includes

- 4-ft. 5-15P to C13 Power Cord with Red Connectors

### Description

Tripp Lite's line of Color-Coded AC Power Cords offer quick identification of your computer cables. This 4-ft. cable with red connectors will replace the power cable on most computers and peripherals that have a removable power cord. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. UL Listed.

### Features

- Red color-coded 5-15P to C13 connectors
- 4-ft replacement power cable for a PC, printer, monitor, etc.
- 18AWG, 10AMP, 125Volt
- UL Listed

## Specifications

INPUT	
Cable Length (ft.)	4
Cable Length (m)	1.2
PHYSICAL	
Color	Black; Red
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Operating Humidity Range	10 - 85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>