

6-Outlet Surge Protector, Direct Plug-In, 540 Joules, Diagnostic LED, Black Casing

MODEL NUMBER: **SK6-0B**



Highlights

- 6 outlets/direct plug-in
- 540 joule rating
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- SK6-0B Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0B Surge Suppressor is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features 6 outlets and 540 joules of surge energy absorption. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 6 outlets: direct plug-in
- Surge energy absorption: 540 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Holds up to 4 large transformer plugs
Right-Angle Outlets	No
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V



Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Right-Angle Plug	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	150
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	400, 500, 500
Immunity	Conforms to IEE 587/ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.28 x 6.72 x 2.60
Shipping Dimensions (hwd / cm)	23.57 x 17.07 x 6.60
Shipping Weight (lbs.)	.55
Shipping Weight (kg)	0.25
Unit Dimensions (hwd / in.)	4.8 x 4.6 x 1.2
Unit Dimensions (hwd / cm)	12.19 x 11.68 x 3.05
Unit Weight (lbs.)	.406
Unit Weight (kg)	0.18
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Receptacle Color	Black
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL 1449 3rd Edition
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>