

## Waber-by-Tripp Lite Industrial Power Strip with 6 Right-Angle Outlets, 15-ft. Cord, Mounting Tabs

MODEL NUMBER: **UL24RA-15**



### Highlights

- 6 outlets turned 90 degrees
- 12.5" length
- 15 ft. cord
- Lighted master switch

### Package Includes

- UL24RA-15 Power Strip
- Warranty information
- Instruction manual

### Description

The Waber-by-Tripp Lite UL24RA-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center spacing, 15 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Right angle outlet orientation better accommodates large transformer plugs. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL24RA-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 15 amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-15P/Output: 6 NEMA 5-15R

ELECTRICAL - 120VAC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R output receptacles with 1.625 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- Right angle outlet orientation better accommodates large transformer plugs
- UL1363 (USA), cUL (Canada)
- 15 amp power handling capacity with circuit breaker
- 15 foot AC line cord

## Specifications



<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Outlet Spacing	1.625 in.
Outlet Orientation	Single row of 6 arranged with right-angle outlet orientation
Right-Angle Outlets	Yes
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	Nema 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5 (h with mounting tabs - 13.75)
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8 (h with mounting tabs - 34.93)
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	41.3mm
Keyhole Slot Mounting Measurement (Center to Center)	261.92mm
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>