

Protect It! 8-Outlet Home Computer Surge Protector, 8-ft. Cord, 1080 Joules, Space-Saving Plug

MODEL NUMBER: **SK6-6**



Highlights

- 8 outlets / 8-ft. cord
- 1080 joule rating
- \$35,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

Package Includes

- SK6-6 Surge Suppressor
- Child Safety Covers
- Color-coded cord identifiers
- Warranty information and Instruction manual

Description

The SK6-6 Surge Suppressor from Tripp Lite has 8 outlets and an 8-ft. cord with a space-saving right-angle plug. The unit has 1080 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. \$35,000 Ultimate Lifetime Insurance (USA and Canada Only). The SK6-6 comes with child safety covers and color-coded cord identifiers.

Features

- 8 outlets with child safety covers
- 8-ft. cord with space-saving right-angle plug
- \$35,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment -
- Surge energy absorption: 1080 joules; 54,500 amps
- 15 amp circuit breaker
- 3 diagnostic LEDs indicate AC present, grounded & protection present
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers

Specifications

| OUTPUT | |
|-------------------------|------------|
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (8) 5-15R |
| Output (Watts) | 1800 |



| | |
|--|--|
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | Holds up to 4 large transformer plugs |
| Right-Angle Outlets | No |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P input plug |
| Input Plug Features | Space-saving right angle plug |
| Input Cord Length (ft.) | 8 |
| Input Cord Length (m) | 2.4 |
| Voltage Compatibility (VAC) | 120 |
| Right-Angle Plug | Yes |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Two position red illuminated on/off power switch |
| Diagnostic LED Details | PROTECTION PRESENT (green), GROUNDED (red) and LINE OK (green) |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1080 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 140 |
| AC Suppression Surge Current Rating | 54,500 amps |
| UL1449 Let Through Rating | 400V - UL Verified |
| Immunity | Conforms to IEE 587 / ANSI C62.41 |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Unit Dimensions (hwd / in.) | 1.5 x 2.5 x 13 |
| Unit Dimensions (hwd / cm) | 3.8 x 6.4 x 33 |
| Material of Construction | Plastic |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Integrated Keyhole Mounting Tabs | Keyhole mounting tabs enable wall mounting |
| Housing Color | Light Gray |
| Receptacle Color | Light Gray |
| Color (AC Line Cord) | Light Gray |
| Outlets Measurement (Center to Center) | 28.6mm |
| Keyhole Slot Mounting Measurement (Center to Center) | 114.3mm |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$35,000 Ultimate Lifetime Insurance |

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>