

## HDBaseT HDMI over Cat5e/6/6a Extender Receiver, Serial and IR, 4K x 2K UHD/1080p, Up to 500 ft. (150 m), TAA

MODEL NUMBER: **BHDBT-R-SI-ER**



### Description

The BHDBT-R-SI-ER HDBaseT Extender Receiver works in tandem with the Tripp Lite BHDBT-Series matrix transmitter in your HDBaseT installation to extend uncompressed HDMI video and audio, RS-232 serial and IR remote control signals.

Using a single Cat5e/6/6a cable, the BHDBT-R-SI-ER can extend a 1920 x 1080 (1080p) signal up to 500 feet (150 m). To further extend and expand your installation, you can insert up to five [BHDBT-TR-SI-ER](#) Extender Transceivers between the receiver and transmitter for a total range up to 3,000 feet (1080p) with a monitor connected to each transceiver.

You can control RS-232 serial devices, such as touchscreen displays or scanners, at baud rates up to 115 Kbps. The 2-way IR Remote Control feature (@ 39 KHz) lets you also control your Blu-ray player using its remote when at the remote monitor and vice versa. The monitor connects to the rear locking HDMI port (ideal for use with Tripp Lite's [P569-006-LOCK](#) High-Speed HDMI cables with locking connectors) that prevents the cable from coming loose or undone, ensuring an intact signal.

The BHDBT-R-SI-ER supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP. Included mounting hardware lets you attach the receiver to a wall, rack or pole. Sets up quickly with no software to download or install.

### Features

#### Supports the Latest Video and Audio Applications

- Connects to Tripp Lite BHDBT-Series matrix transmitter with a single Cat5e/6/6a cable
- Extends a High Definition 1920 x 1080 (1080p) @ 60 Hz signal up to 500 ft. (150 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio
- Supports 36-bit Deep Color (12 bits per channel), CEC pass-through, 3D video, EDID and HDCP
- Add up to 5 [BHDBT-TR-SI-ER](#) Extender Transceivers to further expand the range of your installation up to 3,000 ft. (1080p) with a monitor attached to

### Highlights

- Extends a 1080p @ 60 Hz signal up to 500 ft. (150 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Locking HDMI port ensures an intact signal
- Mounts easily to wall, rack or pole
- Plug and play—no software or drivers to install

### Package Includes

- BHDBT-R-SI-ER HDBaseT HDMI over Cat5e/6/6a Extender Receiver
- IR-IN cable
- IR-OUT cable
- 3.5 mm Male to DB9 Female adapter cable
- 3.5 mm Male to DB9 Male adapter cable
- External Power Supply with NEMA 1-15P Plug (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 3A)
- Mounting hardware
- Owner's Manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

each transceiver

#### Allows You to Control Other Devices

- 2-way 39 KHz IR Remote Control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)
- RS-232 serial port supports 115 Kbps full-duplex baud rates for devices such as scanners and touchscreen monitors

#### Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Included mounting hardware lets you install each unit on a wall, rack or pole
- Locking HDMI port (ideal for use with Tripp Lite's [P569-006-LOCK](#) HDMI cables) prevents cable from coming loose or disconnected, ensuring an intact signal

#### TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A
PHYSICAL	
Unit Dimensions (hwd / in.)	1.1 x 4.5 x 2.5
Included Mounting Accessories	Y
Color	Black
Unit Weight Details	0.55lbs
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	500
Max 480P Range (ft)	500
Max 1440 x 900 Range (ft)	500
Max 1080i Range (ft)	500
Max 1080P Range (ft)	500
Max 480i Range (ft)	500
Max 640 x 480 Range (ft)	500



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Max 800 x 600 Range (ft)	500
Max 1600 x 1200 Range (ft)	500
Max 720P Range (ft)	500
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
10/100 Ethernet Extension Support	No
<b>CERTIFICATIONS</b>	
Approvals	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>