

HDBaseT HDMI over Cat5e/6/6a Extender Receiver, Serial and IR, 4K x 2K @ 30Hz UHD / 1080p @ 60Hz, Up to 328 ft. (100 m), TAA

MODEL NUMBER: BHDBT-R-SI-LR



Description

The BHDBT-R-SI-LR HDBaseT Extender Receiver works in tandem with the Tripp Lite BHDBT-Series matrix transmitter in your HDBaseT installation to extend uncompressed HDMI video and audio, RS-232 serial and IR remote control signals.

Using a single Cat5e/6/6a cable, the BHDBT-R-SI-LR can extend a 1920 x 1080 (1080p) signal at 60 Hz or an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) at 30Hz video signal up to 328 feet (100 m). To further extend and expand your installation, you can insert up to five [BHDBT-TR-SI-LR](#) Extender Transceivers between the receiver and transmitter for a total range up to 2,000 feet (610 m) with a monitor connected to each transceiver.

You can control RS-232 serial devices, such as touchscreen displays or scanners, at baud rates up to 115 Kbps. The 2-way IR Remote Control feature (@ 39 KHz) lets you also control your Blu-ray player using its remote when at the remote monitor and vice versa. The monitor connects to the rear locking HDMI port (ideal for use with Tripp Lite's [P569-006-LOCK](#) High-Speed HDMI cables with locking connectors) that prevents the cable from coming loose or undone, ensuring an intact signal.

The BHDBT-R-SI-LR supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio, as well as 3D video, EDID and HDCP. Included mounting hardware lets you attach the receiver to a wall, rack or pole. Sets up quickly with no software to download or install.

Features

Supports the Latest Video and Audio Applications

- Connects to Tripp Lite BHDBT-Series matrix transmitter with a single Cat5e/6/6a cable
- Extends an Ultra High Definition (UHD) 4096 x 2160 or 3840 x 2160 (4K x 2K) @ 30Hz signal or High Definition 1920 x 1080 (1080p) @ 60 Hz signal up to 328 ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD audio

Highlights

- Extends both a 4096 x 2160 and 3840 x 2160 (4K x 2K) @ 30Hz signal up to 328 ft. (100 m)
- Extends a 1080p @ 60 Hz signal up to 328 ft. (100 m)
- Supports 7.1-channel surround sound, DTS-HD and Dolby TrueHD
- Mounts easily to wall, rack or pole
- Plug and play—no software or drivers to install

Package Includes

- BHDBT-R-SI-LR HDBaseT HDMI over Cat5e/6/6a Extender Receiver
- IR-IN cable
- IR-OUT cable
- 3.5 mm Male to DB9 Female adapter cable
- 3.5 mm Male to DB9 Male adapter cable
- External Power Supply with NEMA 1-15P Plug (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V, 3A)
- Mounting hardware
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports 36-bit Deep Color (12 bits per channel), CEC pass-through, 3D video, EDID and HDCP
- Add up to 5 [BHDBT-TR-SI-LR](#) Extender Transceivers to further expand the range of your installation up to 2,000 ft. (610 m) with a monitor attached to each transceiver

Allows You to Control Other Devices

- 2-way 39 KHz IR Remote Control functionality lets you control your Blu-ray player with its remote while standing at the remote monitor (and vice versa)
- RS-232 serial port supports 115 Kbps full-duplex baud rates for devices such as scanners and touchscreen monitors

Easy to Set Up and Use

- Plug-and-play engineering—no software or drivers to download and install
- Included mounting hardware lets you install each unit on a wall, rack or pole
- Locking HDMI port (ideal for use with Tripp Lite's [P569-006-LOCK](#) HDMI cables) prevents cable from coming loose or disconnected, ensuring an intact signal

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 3A
PHYSICAL	
Unit Dimensions (hwd / in.)	1.1 x 4.5 x 2.5
Included Mounting Accessories	Y
Color	Black
Unit Weight Details	0.55lbs
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
COMMUNICATIONS	
Max 1024 x 768 Range (ft)	328
Max 480P Range (ft)	328
Max 1440 x 900 Range (ft)	328
Max 1080i Range (ft)	328
Max 1080P Range (ft)	328



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Max 1920 x 1440 Range (ft)	328
Max 2560 x 1600 Range (ft)	328
Max 4K UHD Range (ft)	328
Max 480i Range (ft)	328
Max 640 x 480 Range (ft)	328
Max 800 x 600 Range (ft)	328
Max 1600 x 1200 Range (ft)	328
Max 1920 x 1200 Range (ft)	328
Max 2048 x 1536 Range (ft)	328
Max 720P Range (ft)	328
CONNECTIONS	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
FEATURES & SPECIFICATIONS	
IR Remote Extension Support	Yes
RS-232 Serial Extension Support	Yes
10/100 Ethernet Extension Support	No
CERTIFICATIONS	
Approvals	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>