

Dual Full Motion Flex Arm Desk Clamp for 13" to 27" Monitors

MODEL NUMBER: DDR1327DCS



Description

The VESA-compliant DDR1327DCS Dual Full Motion Flex Arm Desk Clamp attaches to your desk, table or workstation, allowing you to mount two monitors above it and free up valuable workspace. Ideal for home and office, the DDR1327DCS fits most flat-panel displays from 13 to 27 inches.

Dual swivel arms can be independently adjusted for angle and height to give you maximum flexibility in positioning your monitors to fit your environment and comfort level - Note: Arms cannot be positioned directly across from each other.. Move a screen closer to you, or push both screens out of your way when not in use. A 180° swivel and -80° to +90° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your monitors in portrait or landscape orientation.

Durable clamp attaches to most flat surfaces up to 2.4 inches thick for a firm grip. Each swivel arm supports up to 22 pounds. The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Attaches to Most Desks, Tables and Workstations

- Clamps securely to most flat surfaces from 0.4 in. to 2.4 in.
- Fits most flat-panel displays from 13 to 27 in.
- Dual swivel arms adjust independently for angle and height - Note: Arms adjust independently and cannot be positioned directly across from each other
- Ideal for home and office use

Convenient One-Touch Adjustment

- 180° swivel and -80° to +90° tilt capability provides comfortable viewing from multiple angles
- Full 360° rotation for viewing in portrait or landscape orientation

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 5-year warranty
- 180° swivel and -80° to +90° tilt for wide range of motion
- Each swivel arm supports up to 22 lb.

Package Includes

- Desk mount assembly
- End cap
- (2) Arms
- (2) Mounting assemblies
- (3) Collars
- (2) Sleeves
- (2) Knobs
- (8) M4 screws
- (8) M5 screws
- (8) Washers
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual



Durable Metal Construction

- Each swivel arm supports up to 22 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Mounting hardware included

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

PHYSICAL	
Mounting Location	Desk Clamp
Unit Dimensions (hwd / in.)	12.52 x 33.86 x 4.45
Unit Dimensions (hwd / cm)	31.80 x 86.0 x 11.30
Unit Weight (lbs.)	6.56
Unit Weight (kg)	2.98
Material of Construction	Steel
Color	Black; Silver
Screen Size Compatibility (in.)	13 - 27
Screen Size Compatibility (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-80/+90 Tilt; 180 swivel; 360 rotate
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>