

Swivel/Tilt Wall Mount w/Screen Adjustment for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SP



Description

The VESA-compliant DWM1327SP Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be independently adjusted for angle and height to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with soft rubber-feel finish supports up to 33 pounds. Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

Features

Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 13 to 27 in.
- Ideal for home, office, hotels, bars and restaurants
- Full-motion swivel arm adjusts independently for angle and height
- Mounting hardware included

Convenient One-Touch Adjustment

- 180° swivel, -15° to +15° tilt and -2° to +2° screen level adjustment capability provides comfortable viewing from multiple angles

Durable Metal Construction

- Supports up to 33 lb.
- Soft rubber-feel finish with decorative covers blends with any décor
- Fully assembled for immediate installation

Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel, -15° to +15° tilt and -2° to +2° screen adjustment
- 5-year warranty
- Supports up to 33 lb.

Package Includes

- DWM1327SP Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Washers
- (3) Anchor bolts
- (3) Concrete anchors
- Wrench
- Hex key, 4 mm
- Hex key, 6 mm
- Owner's manual



- Display cable attaches to mount to reduce clutter

VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

Specifications

PHYSICAL	
Mounting Location	Wall
Unit Dimensions (hwd / in.)	7.48 x 18.69 x 5.20
Unit Dimensions (hwd / cm)	19 x 47.5 x 13.2
Unit Weight (lbs.)	8.64
Unit Weight (kg)	3.92
Color	Black
Screen Size Compatibility (in.)	13 - 27
Screen Size Compatibility (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 Swivel; -2/+2 Level Adjustment
Min/Max Arm Extension (in.)	2.16 - 22.85
Min/Max Arm Extension (cm)	5.49 - 58.04
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>