

## Tilt Wall Mount for 60" to 100" TVs and Monitors

MODEL NUMBER: DWT60100XX



### Description

The VESA-compliant DWT60100XX Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants, it fits most flat-panel displays from 60 to 100 inches. A  $-15^{\circ}$  to  $+15^{\circ}$  tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Low-profile mount is concealed behind the display to give a sleek, professional appearance. Display brackets with connected straps adjust to compensate for off-center wall studs. Durable all-metal frame with scratch-resistant powder-coated finish supports up to 350 pounds. Mounting hardware included. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm, 800 x 400 mm, 800 x 600 mm, 800 x 800 mm, 1000 x 400 mm, 1000 x 600 mm and 1000 x 800 mm.

### Features

#### Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 60 to 100 in.
- Ideal for home theaters, classrooms, boardrooms, hotels, bars and restaurants
- Mounts out of sight behind display for sleek, professional appearance
- Mounting hardware included
- Tested in accordance with UL Standard 2442

#### Convenient One-Touch Adjustment

- $-15^{\circ}$  to  $+15^{\circ}$  tilt capability provides comfortable viewing from multiple angles
- Improves viewing angles in applications where audience is below the display

#### Durable Metal Construction

- Supports up to 350 lb.

### Highlights

- Fits most flat-panel displays from 60 to 100 in.
- Hangs out of sight for a sleek, professional appearance
- $-15^{\circ}$  to  $+15^{\circ}$  tilt capability for wide range of motion
- 5-year warranty
- Supports up to 350 lb.

### Package Includes

- Wall plate
- Mounting template
- (2) Adapter brackets
- (2) Tilt adjusting knobs
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (4) Big spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Owner's manual



- Adjustable display brackets with connected straps compensate for off-center wall studs
- Scratch-resistant powder-coated finish

#### VESA Compliance

- Supports the following VESA mounting hole patterns: 200 x 200 mm, 300 x 300 mm, 400 x 200 mm, 400 x 400 mm, 600 x 400 mm, 800 x 400 mm, 800 x 600 mm, 800 x 800 mm, 1000 x 400 mm, 1000 x 600 mm and 1000 x 800 mm

## Specifications

PHYSICAL	
Mounting Location	Wall
Unit Dimensions (hwd / in.)	32.76 x 44.88 x 5.12
Unit Dimensions (hwd / cm)	83.2 x 113.0 x 113.0
Unit Weight (lbs.)	17.36
Unit Weight (kg)	7.87
Color	Black
Screen Size Compatibility (in.)	60 - 100
Screen Size Compatibility (cm)	152.4 - 254
VESA Pattern (mm)	200x200; 300x300; 400x200; 400x400; 600x400; 800x400; 800x600; 1000x400; 1000x600; 1000x800
Motion	Tilt
Degrees of Motion	-15/+15
Maximum Weight Capacity (lbs.)	350
Maximum Weight Capacity (kg)	159
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>