

Protect It! Surge Protector with 6 Right Angle Outlets, 6 ft. Cord, 540 Joules, Diagnostic LED

MODEL NUMBER: **SPIKESTIK**



Highlights

- 6 right-angle outlets
- 6 ft. cord
- 540 joule rating
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- SPIKESTIK Surge Suppressor
- Child Safety Covers
- Instruction manual and Warranty information

Description

The SPIKESTIK Surge Suppressor from Tripp Lite has 6 right-angle outlets and a 6-ft. cord. The unit has 540 joules of surge energy absorption to handle the strongest surges.

Features

- 6 right-angle outlets
- 6-ft. cord
- Surge energy absorption: 540 joules; 27,000 amps
- 15 amp circuit breaker
- EMI/RFI noise filtering
- Keyhole supports for wall mounting
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada & Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Holds up to 3 large transformer plugs
Right-Angle Outlets	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P input plug
Input Cord Length (ft.)	6
Input Cord Length (m)	1.8 m
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Right-Angle Plug	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Two position on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
AC Suppression Surge Current Rating	27,000 amps
UL1449 Let Through Rating	400V - UL Verified
Immunity	Conforms to IEE 587 / ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	10.25 x 2.70 x 1.52
Unit Dimensions (hwd / cm)	26 x 6.9 x 3.9
Material of Construction	Plastic
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlets Measurement (Center to Center)	28.6mm
Keyhole Slot Mounting Measurement (Center to Center)	114.6mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>