

3300 Series (Fire-Rated) 8300 Series (Life-Safety) Mortise Exit Device



3300 SERIES					
MODEL	TYPE	FIRE RATING	DOOR CONSTRUCTION	MAX SIZE SINGLE DOORS	MAX SIZE PAIRS & DOUBLE EGRESS
3300	Single Point Mortise	3 Hr	Hollow metal or wood	4'0" x 8'0"	8'0" x 8'0"**

*May be used with 3100 or 3600 Series with an open back strike.

Features

- Heavy duty deadlatching mechanism
- Strong, durable construction for a high level of security
- Easy to install
- Clean, unobtrusive design
- Pushbar clad or anodized, not plated, in a variety of finishes

Specifications

3300 SERIES CERTIFICATIONS:

- UL Panic-Fire Exit Hardware, 3-Hour Fire Label
- UL 305 Panic Hardware
- California State Fire Marshall
- New York City MEA*
- Warnock/Hersey Listing

8300 SERIES CERTIFICATIONS:

- UL 305 Panic Hardware
- ANSI/BHMA A156.3 Grade 1
- California State Fire Marshall
- New York City MEA*

*Consult Factory for specific number

MATERIALS

- Pushbar made of extruded aluminum, clad, or anodized in a variety of finishes.

HANDING

- Specify handing and bevel if applicable. Lever Entry Trim is field reversible.

PUSHBAR LENGTH

- Standard sizes: dimensioned for 30", 36", 42", and 48" openings. Standard width bars can be field cut to the next smallest opening width.

DOOR THICKNESS

- Suits 1-3/4" standard. Can be modified for thicker doors.

STILE WIDTH

- 3300 – Minimum 5". Door construction may require additional stile width to meet fire ratings and provide adequate strength.
- 8300 – Minimum 5".

PROJECTION

- 2-5/8" when fully projected, 1-5/8"when dogged.

DOGGING

- Standard dogging with hex key or cylinder dogging for 8300 Series only. Electric dogging also available for 3300 and 8300 Series.

FASTENERS

- Standard self-tapping screws. Optional Sex Bolt Kits 26-0584 (two required per device). Specify finish.

STRIKES

- Made of stainless steel. Supplied with exit device. See additional information below.

CYLINDERS

- See CYLINDERS section of this catalog for cylinder make, thumbturn and trim ring information. (Available separately).

CYLINDER X FIXED PULL (FUNCTION 03)

- Accepts any standard mortise cylinder with MS® cam.

3080 ENTRY TRIM (FUNCTIONS 08, 09)

- Accepts any standard diameter mortise cylinder with MS cam. Accommodates cylinder lengths from 1" to 1-1/4". (Available separately).

WARRANTY

- Five year limited.

3300 FIRE-RATED/8300 LIFE-SAFETY

- Heavy –duty deadlatch fits ANSI A115.1 standard door and jamb prep. 2-3/4" backset.

Strikes

- A variety of strikes are available for different conditions and applications.
- Standard strike (included).
- Extended Lip 8360-XX (available separately).
- Open Back 4009-01 (available separately).

Thick Door Kits (8300 Only)

- 91-0995-02* - 2" Thick Door Kit
- 91-0995-03* - 2-1/4" Thick Door Kit
- 91-0995-04* - 2-1/2" Thick Door Kit
- 91-0995-05* - 2-3/4" Thick Door Kit
- 91-0995-06* - 3" Thick Door Kit

*Order 8360-XX Long Lip Strike as required.

