

Basic System Diagram



Model Numbers

- AD2089 120 VAC, 50/60 Hz Desktop
 - AD2089R 120 VAC, 50/60 Hz Rack mount
 - AD2089-1 230 VAC, 50/60 Hz Desktop
 - AD2089R-1 230 VAC, 50/60 Hz Rack mount
- Note: AC wall-type transformer and terminal block supplied (9 VAC for 120 V, 8 VAC for 230 V).*

Connectors

- RJ-45 RS-232, Power

Electrical

- Supply Voltage
 - AD2089 Series 120 VAC, 50/60 Hz
 - AD2089-1 Series 230 VAC, 50/60 Hz
- Power Consumption 5.0 watts (nominal)
- Non-Volatile Memory User-defined programming stored in EEROM indefinitely

Mechanical

- Dimensions (H x W x D)
 - Desktop 76.2 x 419 x 133 mm
(3.0 x 16.5 x 5.25 in)
 - Rack Mount 133.4 x 482.6 x 38.1 mm
(5.25 x 19 x 1.5 in)
- Weight 2.55 kg (5.5 lbs)
- Shipping Weight 3.65 kg (8.0 lbs)
- Color Black

Environmental

- Operating Temperature 0° to 40°C (32° to 104°F)
- Humidity 5-90% RH (non-condensing)
- Storage Temperature -40° to 70°C (-40° to 155°F)

Regulatory

- Emissions FCC Part 15, Subpart B Class A
CE: EN55022 Class B
- Immunity CE: EN50082-1
- Safety UL2044
CSA 22.2 No. 1 (cUL)
CE: EN60950

Product offerings and specifications are subject to change without notice. Actual products may vary from photos. Not all products include all features. Availability varies by region; contact your sales representative. Certain product names mentioned herein may be trade names and/or registered trademarks of other companies.

