

DOOR LOCKS

| | | | | | | | |
|----------------|---|---------|--|-----------|---|----------|--|
| Saturn | Sedan, Coupe, Wagon | 1997-02 | Replacement locks available from Saturn dealers only Use face cap P-49-201 Use tumbler series P-49-101/104 | | | | |
| Saturn | Astra | 2008 | Replacement locks available from Saturn dealers only Use tumbler series P-23-121/134 | | | | |
| Saturn | Aura | 2007-08 | Uncoded service pack | D-41-003 | Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new. | | |
| Saturn | Ion | 2003-07 | Replacement locks available from Strattec | | | | |
| Saturn | L-series | 2002-05 | Replacement locks available from Saturn dealers only Use tumbler series P-49-101/104 | | | | |
| Saturn | Outlook | 2007-08 | Uncoded service pack | D-41-003 | Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new. | | |
| Saturn | Relay | 2005-07 | Locks using B106 keys, available from Saturn / GM dealers only. Use tumbler series P-41-011/015 | | | | |
| | | | Locks using B86 keys, available from Strattec Use tumbler series P-41-161/164 | | | | |
| Saturn | Sky | 2007-08 | Replacement locks available from Strattec. | | | | |
| Saturn | VUE | 2002-07 | Uncoded service pack | D-41-003 | Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new. Locks originally installed on the car usually use tumbler series P-41-111/114 | | |
| Saturn | VUE | 2008 | no lock cylinder on right side | | Complete lock LH | D-50-120 | Use tumbler series P-13-101/104 (P-21-111/114) |
| Scion | TC | 2005-08 | Complete lock RH | D-30-541 | Complete lock LH | D-30-542 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Scion | XA | 2004-06 | Complete lock RH | D-30-535 | Complete lock LH | D-30-536 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Scion | XB | 2004-06 | Complete lock RH | D-30-537 | Complete lock LH | D-30-538 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Scion | XB | 2008 | no lock cylinder on RH side | | Complete lock LH | D-30-544 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Scion | XD | 2008 | no lock cylinder on RH side | | Complete lock LH | D-30-560 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Skoda | 105, 120, 130 | All | Coded pair complete locks including pawls | DP-45-101 | Disassembly and rekeying these locks is not recommended | | |
| Sterling | Sedan | 1987-91 | Complete lock RH | D-14-221 | Complete lock LH | D-14-222 | Use tumbler series P-14-121/125 |
| Sterling Truck | 360 | All | Replacement locks available from Sterling truck dealers only Use tumbler series P-30-161/164 | | | | |
| Sterling Truck | Bullet | All | Replacement locks available from Sterling truck dealers only Use tumbler series P-44-111/114 | | | | |
| Sterling Truck | Cargo | 1997-up | Complete lock RH | D-14-143 | Complete lock LH | D-14-144 | Tumblers are not available. |
| Sterling Truck | With Ford locks Acterra, A-Line, L-Line, others | 1997-08 | See Ford Truck – other models, for all variations. | | | | |
| Studebaker | All | All | Try classic Studebaker parts suppliers. | | | | |
| Subaru | All | 1972-74 | Uncoded service pack X6 / 62DT keyway | D-16-202 | If original pawl cannot be reused, use P-16-301 (RH & LH) Use face cap P-16-204 Use tumbler series P-16-141/144 (P-16-151/154) | | |
| Subaru | Sedan | 1975-79 | Uncoded service pack X6 / 62DT keyway | D-16-202 | If original pawl cannot be reused, use P-16-301 (RH & LH) Use face cap P-16-204 Use tumbler series P-16-141/144 (P-16-151/154) | | |
| Subaru | Hatchback | 1980-89 | Coded lock | D-29-101 | If original pawl cannot be reused, use P-16-335 (RH) or P-16-336 (LH) Use chrome face cap P-16-205, or black face cap P-16-206 Use tumbler series P-16-141/144 (P-16-151/154) | | |
| Subaru | Sedan | 1980-84 | Coded lock | D-29-101 | If original pawl cannot be reused, use P-16-335 (RH) or P-16-336 (LH) Use chrome face cap P-16-205, or black face cap P-16-206 Use tumbler series P-16-141/144 (P-16-151/154) | | |
| Subaru | DL, GL, GL10, Loyale | 1985-94 | Complete lock RH | D-29-103 | Complete lock LH | D-29-104 | Use tumbler series P-16-161/164 |
| Subaru | Baja | 2003-06 | Replacement locks available from Subaru dealers only Use tumbler series P-16-181/184 | | | | |
| Subaru | B9 Tribeca | 2006-07 | Replacement locks available from Subaru dealers only Use tumbler series P-16-181/184 | | | | |
| Subaru | Brat | 1977-87 | Coded lock | D-29-101 | If original pawl cannot be reused, use P-16-335 (RH) or P-16-336 (LH) Use chrome face cap P-16-205, or black face cap P-16-206 Use tumbler series P-16-141/144 (P-16-151/154) | | |
| Subaru | Forester | 1998-07 | Complete lock with pawl reversible R&L | D-16-129 | Use face cap P-16-213 Use tumbler series P-16-181/184 | | |
| Subaru | Impreza | 1993-01 | Coded lock, designed to clip a switch on top (switch not included) | D-16-223 | If original pawl cannot be reused, use P-29-301 (reversible RH & LH) Use face cap P-16-205 Use tumbler series P-16-161/164 | | |
| Subaru | Impreza | 2002-07 | Replacement locks available from Subaru dealers only Use tumbler series P-16-181/184 | | | | |
| Subaru | Impreza | 2008 | Replacement locks available from Subaru dealers only Tumblers not currently available. | | | | |

Check www.carlocks.com for the most up to date information

DOOR LOCKS

| | | | | | | | |
|--------|------------------------------|---------|---|---------------------|--|-----------|---|
| Suzuki | XL-7 | 2007-08 | Uncoded service pack | D-41-003 | Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new. | | |
| Toyota | Avalon | 1995-99 | Complete lock RH | D-30-129 | Complete lock LH (no lighted keyhole) | D-30-130 | Use tumbler series P-30-181/188 |
| | | | Lighted keyhole on left side only | | Complete lock LH (lighted keyhole) | D-30-131 | Use tumbler series P-30-181/188 |
| Toyota | Avalon | 2000-04 | Complete lock RH | D-30-517 | Complete lock LH | D-30-518 | Use tumbler series P-30-181/188 |
| Toyota | Avalon | 2005-07 | no lock cylinder on RH side | | Complete lock LH cars with SmartKey | D-30-546 | Use tumbler series P-30-121/123 |
| | | | | | For cars without SmartKey replacement locks available from Toyota dealers only. Use tumbler series P-30-131/134 | | |
| Toyota | Camry | 1983-91 | Lock service package | D-30-207 (D-30-107) | Door lock pair including pawls | DP-30-107 | If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144 |
| | | | Lighted keyhole on left side only | | Complete lock LH with lighted keyhole | D-30-120 | Use face cap P-30-205 Use tumbler series P-30-141/144 |
| Toyota | Camry | 1992-96 | Complete lock RH | D-30-109 | Complete lock LH (no lighted keyhole) | D-30-110 | Use face cap P-30-219 Use tumbler series P-30-181/188 |
| | | | Lighted keyhole on left side only | | Complete lock LH with lighted keyhole | D-30-128 | Use face cap P-30-219 Use tumbler series P-30-181/188 |
| Toyota | Camry | 1997-01 | Complete lock RH | D-30-152 | Complete lock LH | D-30-153 | Use face cap P-30-265 Use tumbler series P-30-181/188 |
| Toyota | Camry | 2002-06 | Complete lock RH | D-30-529 | Complete lock LH | D-30-530 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Toyota | Camry | 2007-08 | Complete lock RH except Hybrid and cars with Smartkey | D-30-541 | Complete lock LH except Hybrid and cars with Smartkey | D-30-542 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| | | | Hybrid and cars with Smartkey no lock cylinder on RH side | | Complete lock LH Hybrid and cars with Smartkey only | D-30-556 | Use face cap P-30-268 Use tumbler series P-30-121/123 |
| Toyota | Camry Solara | All | see Solara | | | | |
| Toyota | Carina | 1972-73 | Complete lock with reversible pawl R/L | D-30-101 | Door lock pair | DP-30-101 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Celica | 1970-77 | Complete lock with reversible pawl R/L | D-30-101 | Door lock pair | DP-30-101 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Celica | 1978-81 | Complete lock with reversible pawl R/L | D-30-104 | Door lock pair | DP-30-104 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Celica | 1982-83 | Complete lock RH | D-30-121 | Complete lock LH | D-30-122 | Use face cap P-30-212 (RH) Use face cap P-30-213 (LH) Use tumbler series P-30-141/144 |
| Toyota | Celica | 1984-85 | Complete lock RH | D-30-116 | Complete lock LH | D-30-117 | Use face cap P-30-261 Use tumbler series P-30-141/144 |
| Toyota | Celica coupe | 1986-89 | Complete lock RH | D-30-142 | Complete lock LH | D-30-143 | Use tumbler series P-30-141/144 |
| Toyota | Celica liftback | 1986-89 | Uncoded plug | D-30-339 | Complete locks previously sold as D-30-160 (RH) and D-30-161 (LH), discontinued when out. Use tumbler series P-30-151/157 | | |
| Toyota | Celica coupe | 1990-93 | Lock service pack | D-30-111 | The original pawl must be reused. Use tumbler series P-30-161/164 | | |
| Toyota | Celica liftback | 1990-93 | Complete lock RH | D-30-164 | Complete lock LH | D-30-165 | Use tumbler series P-30-151/157 |
| Toyota | Celica | 1994-99 | Complete lock (includes pawl for left side) | D-30-127 | NOTE: D-30-127 includes left side pawl. For right side the original pawl must be reused. Use tumbler series P-30-181/188 | | |
| Toyota | Celica | 2000-05 | Complete lock RH | D-30-519 | Complete lock LH | D-30-520 | Use tumbler series P-30-181/188 |
| Toyota | Corolla except station wagon | 1970-79 | Complete lock with reversible pawl R/L | D-30-101 | Door lock pair | DP-30-101 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Corolla station wagon | 1970-79 | Complete lock with reversible pawl R/L | D-30-166 | Use face cap P-30-201 Use tumbler series P-30-171/174 | | |
| Toyota | Corolla except station wagon | 1980-83 | Complete lock with reversible pawl R/L | D-30-104 | Door lock pair | DP-30-104 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Corolla station wagon | 1980-83 | Complete lock with reversible pawl R/L | D-30-113 | Use face cap P-30-201 Use tumbler series P-30-171/174 | | |
| Toyota | Corolla | 1984-87 | Lock service package | D-30-206 (D-30-106) | Coded pair includes pawls | DP-30-106 | If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144 |
| Toyota | Corolla FX | 1987-88 | Lock service package | D-30-206 (D-30-106) | Coded pair includes pawls | DP-30-106 | If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144 |
| Toyota | Corolla | 1988-92 | Complete lock with reversible pawl R/L | D-30-108 | Door lock pair | DP-30-108 | Use tumbler series P-30-161/164 |
| Toyota | Corolla wagon 2-wheel drive | 1988-92 | Complete lock with reversible pawl R/L | D-30-507 | Use tumbler series P-30-151/157 | | |

Check www.carlocks.com for the most up to date information

DOOR LOCKS

| | | | | | | | |
|--------------|-------------------------|--------------|---|---------------------|--|-----------|---|
| Toyota | Supra | 1979-81 | Complete lock with reversible pawl R/L | D-30-104 | Door lock pair | DP-30-104 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Supra | 1982-83 | Complete lock RH | D-30-121 | Complete lock LH | D-30-122 | Use face cap P-30-212 (RH) Use face cap P-30-213 (LH) Use tumbler series P-30-141/144 |
| Toyota | Supra | 1984-86 | Complete lock RH | D-30-116 | Complete lock LH | D-30-117 | Use face cap P-30-261 Use tumbler series P-30-141/144 |
| Toyota | Supra | 1986 | Complete lock RH | D-30-134 | Complete lock LH | D-30-135 | Use tumbler series P-30-141/144 |
| Toyota | Supra | 1987-89 | Complete lock RH | D-30-136 | Complete lock LH | D-30-137 | Use tumbler series P-30-141/144 |
| Toyota | Supra | 1990-93 | Complete lock RH | D-30-138 | Complete lock LH | D-30-139 | Use tumbler series P-30-161/164 |
| Toyota | Supra | 1993-98 | Complete lock RH | D-30-140 | Complete lock LH | D-30-141 | Use tumbler series P-30-181/188 |
| Toyota | Tercel | 1979-82 | Complete lock with reversible pawl R/L | D-30-104 | Door lock pair | DP-30-104 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota | Tercel | 1983-89 | Lock service package | D-30-206 (D-30-106) | Coded pair includes pawls | DP-30-106 | If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144 |
| Toyota | Tercel liftback | 1987-88 | Coded lock | D-30-162 | If original pawl cannot be reused, use P-30-318 (RH) or P-30-319 (LH) Use tumbler series P-30-151/157 | | |
| Toyota | Tercel liftback | 1989-90 | Coded lock | D-30-163 | If original pawl cannot be reused, use P-30-318 (RH) or P-30-319 (LH) Use tumbler series P-30-151/157 | | |
| Toyota | Tercel sedan | 1987-88 | Coded lock | D-30-118 | If original pawl cannot be reused, use P-30-318 (RH) or P-30-319 (LH) Use tumbler series P-30-141/144 | | |
| Toyota | Tercel sedan | 1989-90 | Coded lock | D-30-119 | If original pawl cannot be reused, use P-30-318 (RH) or P-30-319 (LH) Use tumbler series P-30-141/144 | | |
| Toyota | Tercel | 1991-94 | Uncoded service pack including pawl R&L | D-30-209 | Use tumbler series P-30-151/157 | | |
| Toyota | Tercel | 1995-99 | Complete lock with reversible pawl R/L | D-30-124 | Use face cap P-30-211 Use tumbler series P-30-151/157 | | |
| Toyota | Van Wagon | 1984-90 | Uncoded service pack | D-30-208 | If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-208 Use tumbler series :P-30-171/174 | | |
| Toyota | Yaris hatchback | 2007-08 | Complete lock RH | D-30-559 | Complete lock LH | D-30-560 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Toyota | Yaris sedan | 2007-08 | Complete lock RH | D-30-557 | Complete lock LH | D-30-558 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Toyota truck | Pickup | 1972-78 | Complete lock with reversible pawl R/L | D-30-101 | Door lock pair | DP-30-101 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota truck | Pickup | 1979-83 | Complete lock with reversible pawl R/L | D-30-104 | Door lock pair | DP-30-104 | Use face cap P-30-201 Use tumbler series P-30-141/144 |
| Toyota truck | Pickup | 1984-88 | Lock service package | D-30-206 (D-30-106) | Coded pair | DP-30-106 | If original pawls cannot be reused, use P-30-330 (reversible RH & LH) Use face cap P-30-211 Use tumbler series P-30-141/144 |
| Toyota truck | Pickup | 1989-95 | Complete lock R&L | D-30-112 | Coded pair | DP-30-112 | Use tumbler series P-30-161/164 |
| Toyota truck | T100 | 1993-98 | Complete lock RH | D-30-146 | Complete lock LH | D-30-147 | Use tumbler series P-30-181/188 |
| Toyota truck | Tacoma | 1996-04 | Complete lock RH | D-30-144 | Complete lock LH | D-30-145 | Use face cap P-30-268 Use tumbler series P-30-181/188 |
| Toyota truck | Tacoma | 2005-08 | Complete lock RH | D-30-541 | Complete lock LH | D-30-542 | Use face cap P-30-268 Use tumbler series P-30-131/134 |
| Toyota truck | Tundra | 2000-06 | Complete lock RH | D-30-505 | Complete lock LH | D-30-506 | Use tumbler series P-30-181/188 |
| Toyota truck | Tundra double cab | 2004-06 | Complete lock RH | D-30-527 | Complete lock LH | D-30-528 | Use face cap P-30-219 Use tumbler series P-30-181/188 |
| Toyota truck | Tundra | 2007-08 | If the original shaft (pawl) can be reused, the following locks can be used: D-30-552 for left side (no lock cylinder on the right side) Complete locks including shaft (pawl) are available from Toyota dealers only Use face cap P-30-268 Use tumbler series P-30-131/134 | | | | |
| Triumph | 2000, 2500 4-door sedan | All | Coded plug | D-14-208 | Use tumbler series P-14-221/224 | | |
| Triumph | GT6, Spitfire | up to 1969 | Complete lock with pawl reversible R&L FT code series (62FTkey blank) | D-14-213 | Coded pair with pawls FT code series (62FT key blank) | DP-14-213 | NOTE: Locks using FS code series (62FS key blank) previously available as D-14-211 / DP-14-211 are discontinued when out. |
| Triumph | GT6, Spitfire | 1970-up | Coded plug | D-14-208 | Use tumbler series P-14-221/224 | | |
| Triumph | TR4 | All | Coded plugs (pair) | DP-14-234 | Use tumbler series P-14-201/203 | | |
| Triumph | TR6 | All | Complete lock with pawl reversible R&L FT code series (62FTkey blank) | D-14-213 | Coded pair with pawls FT code series (62FT key blank) | DP-14-213 | NOTE: Locks using FS code series (62FS key blank) previously available as D-14-211 / DP-14-211 are discontinued when out. |
| Triumph | TR7, TR8 | All | Coded plug | D-14-208 | Use tumbler series P-14-221/224 | | |
| TVR | All | All | See the Exotic Brands section | | | | |
| UD Trucks | Most models | All | Lock service package | D-16-206 (D-16-106) | Coded pair | DP-16-106 | Original pawl must be reused Use face cap P-16-205 Use tumbler series P-16-161/164 |
| Volkswagen | Beetle | 8/59 to 7/64 | Complete lock and handle – fits RH & LH | D-31-103 | NOTE: Choice of specific keyway is not available. Use tumbler series P-31-301/305 | | |

ASP PART NUMBERING SYSTEM

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

| | |
|----|--|
| A | Keying kits and parts assortments |
| B | Luggage compartment locks |
| C | Ignition locks |
| D | Door locks (including complete locks that include the door handle) |
| DH | Door handles (except complete locks that include the door handle) |
| DP | Door locks (keyed alike pair) |
| E | Engine compartment locks |
| F | Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.) |
| G | Glove compartment and stowage locks |
| KB | Key blanks |
| P | Lock service parts (including tumblers, face caps, and other parts) |
| RK | Remote head key blanks |
| S | Lock sets |
| T | Fuel tank locks |
| W | Ignition switches (wiring assembly only without lock cylinder) |

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

| | |
|----|---|
| 00 | Various cars |
| 11 | Alfa Romeo |
| 12 | Audi |
| 13 | BMW |
| 14 | British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph) |
| 15 | British Chrysler (Plymouth Cricket, Sunbeam, Hillman) |
| 16 | Nissan / Datsun / Infiniti |
| 17 | Fiat |
| 18 | European Ford (Capri, Fiesta, Merkur) |
| 19 | Honda / Acura |
| 20 | Mazda |
| 21 | Mercedes-Benz |
| 22 | Mitsubishi |
| 23 | GM Europe (Cadillac Catera, Pontiac Lemans, Opel) |

| | |
|----|--|
| 24 | Isuzu (including General Motors brands) |
| 25 | Peugeot |
| 26 | Porsche |
| 27 | Renault |
| 28 | Saab |
| 29 | Subaru |
| 30 | Toyota / Lexus / Scion / Hino truck |
| 31 | Volkswagen |
| 32 | Volvo |
| 33 | Suzuki |
| 34 | Lada |
| 35 | Lancia |
| 36 | Hyundai |
| 37 | Daihatsu |
| 38 | Citroen |
| 39 | Yugo |
| 40 | Kia |
| 41 | General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac) |
| 42 | Ford / Lincoln / Mercury (USA) |
| 43 | American Motors (including some Heavy Trucks and Jeep) |
| 44 | Chrysler / Dodge / Jeep / Plymouth |
| 45 | Skoda |
| 49 | Saturn |
| 50 | Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands) |
| 55 | Renault truck (including some Mack trucks) |
| 56 | Freightliner truck |
| 57 | Kenworth truck |
| 93 | Harley Davidson Motorcycle |
| 94 | Honda Motorcycle |
| 98 | Yamaha Motorcycle |

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

| | |
|----|---|
| DL | Door lock |
| LC | Ignition lock |
| LS | Lock set |
| RP | Lock service parts (including tumblers, face caps, and other parts) |
| SK | Keying kits and parts assortments |
| TL | Luggage compartment locks |

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

PART NUMBER LISTING and POPULARITY RATINGS

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com. This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.