

DOOR LOCKS

Acura	CL	1997-99	Complete lock RH	D-19-112	Complete lock LH	D-19-113	Use tumbler series P-19-141/146
Acura	CL	2001-03	Replacement locks are available from Acura dealers only. Use tumbler series P-19-141/146				
Acura	Integra	1986-89	Uncoded service pack including pawl RH	D-19-208	Uncoded service pack including pawl LH	D-19-209	Use face cap P-19-211 (on handle) Use tumbler series P-19-111/113
Acura	Integra	1990-93	Complete lock RH	D-19-111	Complete lock LH	D-19-110	Use tumbler series P-19-141/146
Acura	Integra	1994-01	Complete lock RH (without correct pawl)	D-19-112	Complete lock RH (without correct pawl)	D-19-113	If original pawl cannot be reused, use P-19-311 (RH) or P-19-312 (LH) Use tumbler series P-19-141/146
Acura	Legend standard trim	1986-90	Uncoded service pack including pawl RH plug length 1.38 inch	D-19-201	Uncoded service pack including pawl LH plug length 1.38 inch	D-19-202	Use face caps (on handle) without lighted keyhole: P-19-216 with lighted keyhole: P-19-219 Use tumbler series P-19-111/113
Acura	Legend L & LS trim level	1986-90	Uncoded service pack including pawl RH plug length 1.46 inch	D-19-208	Uncoded service pack including pawl LH plug length 1.46 inch	D-19-209	Use face caps (on handle) without lighted keyhole: P-19-216 with lighted keyhole: P-19-219 Use tumbler series P-19-111/113
Acura	Legend coupe	1991-95	Replacement locks are available from Acura dealers only. Use tumbler series P-19-141/146				
Acura	Legend sedan	1991-95	Replacement locks are available from Acura dealers only. Face caps to service original locks: without lighted keyhole: P-19-212, with lighted keyhole: P-19-213 Use tumbler series P-19-141/146				
Acura	MDX	2003-08	Replacement locks are available from Acura dealers only. Use tumbler series P-19-160/169				
Acura	NSX	1991-05	Uncoded service pack including pawl RH	D-19-204	Uncoded service pack including pawl LH	D-19-205	Use tumbler series P-19-141/146
Acura	RL	1996-04	Uncoded service pack including pawl RH	D-19-206	Uncoded service pack including pawl LH	D-19-207	Use tumbler series P-19-141/146
Acura	RL	2005-07	Replacement locks are available from Acura dealers only.				
Acura	RSX	2002-06	Replacement locks are available from Acura dealers only. Use tumbler series P-19-141/146				
Acura	SLX	1996-99	Complete lock RH	D-24-105	Complete lock LH	D-24-106	Use tumbler series P-30-161/164
Acura	TL	1995-98	Complete lock RH	D-19-112	Complete lock LH	D-19-113	Use tumbler series P-19-141/146
Acura	TL	1999-03	Replacement locks are available from Acura dealers only. Use tumbler series P-19-141/146				
Acura	TL	2004-07	Replacement locks are available from Acura dealers only.				
Acura	TSX	2004-07	Replacement locks are available from Acura dealers only.				
Acura	Vigor	1992-94	Complete lock RH	D-19-111	Complete lock LH	D-19-110	Use tumbler series P-19-141/146
Alfa Romeo	Alfetta GTV, GTV6	1975-86	Replacement locks are available only from Alfa Romeo dealers or parts specialists				
Alfa Romeo	Alfetta 4-door sedan	1975-79	Complete door handle with lock cylinder RH	D-11-105	Complete door handle with lock cylinder LH	D-11-106	Use tumbler series P-17-121/123
Alfa Romeo	Giulia GT, 105GTV	All	Complete door handle with lock cylinder RH	D-11-103	Complete door handle with lock cylinder LH	D-11-104	Use tumbler series P-17-111/113
Alfa Romeo	GTV	1980-86	Replacement locks are available from Alfa Romeo dealers or parts specialists only.				
Alfa Romeo	Milano	1986-89	3-piece lock set	S-11-106	Ignition lock available only as part of a 3-piece set of complete ignition lock and switch + 2 door locks		
Alfa Romeo	164 sedan	1991-95	Coded plug	D-11-102	Lock housing without plug RH	D-11-401	Lock housing without plug LH D-11-402
Alfa Romeo	Spider	up to 95	Replacement locks are available from Alfa Romeo dealers or parts specialists only.				
American Motors	All	1970-82	Lock service package including pawl (R&L)	D-43-203	Coded pair including pawls	DP-43-103	Use tumbler series P-43-101/115
American Motors	Alliance	1983-87	see Renault Alliance				
American Motors	Concord	1983-84	Lock service package including pawl (R&L)	D-43-203	Coded pair including pawls	DP-43-103	Use tumbler series P-43-101/115
American Motors	Eagle	1983-88	Lock service package including pawl (R&L)	D-43-203	Coded pair including pawls	DP-43-103	Use tumbler series P-43-101/115
American Motors	Encore	1984-87	see Renault Encore				
American Motors	Spirit	1983-84	Lock service package including pawl (R&L)	D-43-203	Coded pair including pawls	DP-43-103	Use tumbler series P-43-101/115
Aston Martin	All	All	see the Exotic Brands section				
Asuna	SE, GT, Passport Optima	1988-92	Uncoded service pack including pawl (R&L)	D-23-208	Plastic pawl retainer: P-23-241 (included with D-23-208, available separately to service original lock, usually destroyed when disassembling) Use tumbler series P-13-101/104 (P-21-111/114)		
Asuna	Sunfire	1990-93	Complete lock RH	D-24-111	Complete lock LH	D-24-112	Use face cap P-30-218 (black) Use tumbler series P-30-161/164
Asuna	Sunrunner	1989-98	Uncoded service pack	D-33-203	Pawls available as follows: right side P-30-322, left side P-30-323 Use face cap P-33-201 Use tumbler series P-33-101/105		
Audi	80,90	1988-92	Complete lock and handle RH (black plastic)	D-12-125	Complete lock and handle LH (black plastic)	D-12-126	These handles are available in black plastic only. If the car has handles of the same color as the car, you can use all of the other parts in the original handle. Use tumbler series P-31-111/114
Audi	80,90	1993-96	Uncoded plug RH	D-12-223	Uncoded plug LH	D-12-224	Use tumbler series P-31-111/114

DOOR LOCKS

GMC trucks	Sprint	1971-77	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
GMC trucks	Suburban	1967-91	Uncoded service pack (chrome)	DL1580U	Coded pair (chrome)	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack (black)	DL1525U	Coded pair (black)	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105
			3-piece lock set (2 front doors + rear door) – chrome only	DL1517	NOTE: DL1517 is used only for Suburban with swing out rear doors. Lock set is not available for Suburban with drop down rear tailgate.		
GMC trucks	Suburban	1992-94	Coded pair	DL1539	Coded 3-piece set 2 front doors + tailgate	DL1518	
			Uncoded service pack	DL1539U	Use tumbler series P-41-101/105		
GMC trucks	Suburban	1995-06	Replacement locks available from Strattec Use tumbler series P-41-161/164				
GMC trucks	Suburban	2007-08	Replacement locks available from Strattec				
GMC trucks	Syclone	All	see S15 Sonoma pickup				
GMC trucks	Top Kick (Medium Duty)	1995-02	Uncoded service pack	DL1539U	Coded pair	DL1539	Use tumbler series P-41-101/105
GMC trucks	Top Kick (Medium Duty)	2003-05	Replacement locks available from Strattec Use tumbler series P-41-161/164				
GMC trucks	Typhoon	All	see Jimmy S15				
GMC trucks	W4, W5 Tiltmaster	1986-87	Coded lock without pawl	D-24-107	If original pawl cannot be reused, use P-30-324 (RH) or P-30-325 (LH) Use face cap P-30-211 Use tumbler series P-24-101/104		
GMC trucks	W4, W5 Tiltmaster	1988-99	Complete lock LH	D-24-118	Right side door lock previously available as D-24-117. Now use D-24-118 and reuse the original right side pawl. Use face cap P-30-211 Use tumbler series P-30-161/164		
GMC trucks	W6, W7 Forward	All	Coded pair (must reuse original pawls)	DP-16-106	NOTE: DP-16-106 is available with DA25 keyway only and cannot be rekeyed to the original B54 key. Locks using the B54 keyway previously available as D-24-108, now available from Chevrolet / GMC / Isuzu truck dealers only. Use face cap P-16-205 (for original locks and DP-16-106) Use tumbler series P-16-161/164 (for original locks and DP-16-106)		
GMC trucks	Yukon	All	see GMC Suburban				
Hino	All	All	See the Heavy Truck section				
Honda	Accord	1976-81	Coded lock with reversible pawl R&L	D-19-102	Use face cap P-19-201 Use tumbler series P-19-111/113		
Honda	Accord	1982-85	Coded lock with reversible pawl R&L	D-19-105	Use face cap P-19-202 Use tumbler series P-19-111/113		
Honda	Accord DX	1986-89	Coded lock with reversible pawl R&L	D-19-108	Use face cap P-19-204 for D-19-108 and some locks originally installed on the car. Some locks originally installed on the car use P-19-217 face cap. Use tumbler series P-19-111/113		
Honda	Accord LX, SE	1986-89	Uncoded service pack including pawl RH	D-19-208	Uncoded service pack including pawl LH	D-19-209	Use face cap P-19-211 (on handle) Use tumbler series P-19-111/113
Honda	Accord	1990-97	Complete lock RH	D-19-112	Complete lock LH	D-19-113	Use face cap P-19-215 (on handle) Use tumbler series P-19-141/146
Honda	Accord	1998-02	Complete lock RH	D-19-120	Complete lock LH	D-19-121	Use tumbler series P-19-141/146
Honda	Accord	2003-08	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	Civic	1975-79	Complete lock with reversible pawl R&L	D-19-101	Use tumbler series P-19-111/113		
Honda	Civic	1980-81	Complete lock with reversible pawl R&L	D-19-102	Use face cap P-19-201 Use tumbler series P-19-111/113		
Honda	Civic	1982-83	Complete lock with reversible pawl R&L	D-19-104	Use face cap P-19-201 Use tumbler series P-19-111/113		
Honda	Civic	1984-87	Complete lock with reversible pawl R&L	D-19-108	Use face cap P-19-204 for D-19-108 and some locks originally installed on the car. Some locks originally installed on the car use P-19-217 face cap. Use tumbler series P-19-111/113		
Honda	Civic	1988-95	Complete Lock RH	D-19-111	Complete lock LH	D-19-110	Use face cap P-19-215 (on handle) Use tumbler series P-19-141/146
Honda	Civic	1996-00	Uncoded service pack including pawl RH	D-19-210	Uncoded service pack including pawl LH	D-19-211	Use tumbler series P-19-141/146
Honda	Civic	2001-02	Complete lock RH	D-19-120	Complete lock LH	D-19-121	NOTE: D-19-120 and D-19-121 do not include switches as used on some cars; switches are available from Honda dealers only. Use tumbler series P-19-141/146
Honda	Civic	2003-08	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	CR-V	1997-01	Uncoded service pack including pawl RH	D-19-210	Uncoded service pack including pawl LH	D-19-211	Use tumbler series P-19-141/146
Honda	CR-V	2002-08	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				

DOOR LOCKS

Honda	CRX	1984-87	Uncoded service pack w/reversible pawl R&L	D-19-203	Use face cap P-19-203 - NOTE there are variations in the diameter of the lock case (for all replacement locks whether sold by ASP or Honda dealers, and locks originally installed on the car when it was new. If P-19-203 is too small diameter for the lock you are working on, file the edge of the lock case until P-19-203 fits properly. This will not affect the fit or function of the lock. Use tumbler series P-19-111/113		
Honda	CRX	1988-91	see Civic				
Honda	Del Sol	1992-95	see Civic				
Honda	Element	2003-08	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	Fit	2007-08	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	Insight	2000-07	Replacement locks available from Honda dealers only Use tumbler series P-19-141/146				
Honda	Odyssey	1995-98	Complete lock RH	D-19-112	Complete lock LH	D-19-113	Use tumbler series P-19-141/146
Honda	Odyssey	1999-04	Complete lock RH	D-19-120	Complete lock LH	D-19-121	NOTE: D-19-120 and D-19-121 do not include switches as used on some cars; switches are available from Honda dealers only. Use tumbler series P-19-141/146
Honda	Odyssey	2005-07	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	Passport made in Japan	1995-97	Uncoded service pack including pawl RH	D-24-203	Uncoded service pack including pawl LH	D-24-204	Use tumbler series P-30-161/164
Honda	Passport made in USA	1995-97	Uncoded service pack including pawl RH	D-24-209	Uncoded service pack including pawl LH	D-24-210	Use tumbler series P-33-101/105
Honda	Passport	1998-02	Uncoded plug	D-19-310	Use tumbler series P-19-141/146		
Honda	Pilot	2003-07	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	Prelude	1979-81	Uncoded plug	D-19-303	Use reversible pawl P-19-354 Use tumbler series P-19-111/113		
Honda	Prelude	1982	Uncoded plug	D-19-304	Use reversible pawl P-19-354 Use tumbler series P-19-111/113		
Honda	Prelude	1983-91	Uncoded plug plastic	D-19-305	Uncoded plug die cast metal	D-19-308	Use tumbler series P-19-111/113
Honda	Prelude	1992-96	Complete lock RH	D-19-111	Complete lock LH	D-19-110	Use tumbler series P-19-141/146
Honda	Prelude	1997-01	Uncoded service pack including pawl RH	D-19-214	Uncoded service pack including pawl LH	D-19-215	Use tumbler series P-19-141/146
Honda	Ridgeline	2006-07	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Honda	S2000	2000-03	Complete lock RH	D-19-120	Complete lock LH	D-19-121	NOTE: D-19-120 and D-19-121 do not include switches as used on some cars; switches are available from Honda dealers only. Use tumbler series P-19-141/146
Honda	S2000	2004-07	Replacement locks available from Honda dealers only Use tumbler series P-19-160/169				
Hummer	H1 (with Ford pin tumbler locks)	All	Uncoded lock chrome	D-42-231	Coded pair	DL1590	Use tumbler series P-42-131/135
			Uncoded lock black	D-42-232	Coded pair	DP-42-148	Use tumbler series P-42-131/135
			Uncoded lock black cap chrome dust cover	D-42-242	Coded pair black cap chrome dust cover	DP-42-104	Use tumbler series P-42-131/135
Hummer	H1 (with Ford 10-cut wafer tumbler locks)	All	Uncoded service pack black cap chrome dust cover	D-42-208	Coded pair, black cap chrome dust cover	DP-42-108	Use face cap P-42-202 (black) Use tumbler series P-42-141/145
Hummer	H2	All	Replacement locks available from Strattec Use tumbler series P-41-161/164				
Hummer	H3	All	Replacement locks available from Hummer / GM dealers only. Use tumbler series P-24-111/114				
Hyundai	Accent	1995-10/97	Complete lock RH	D-36-120	Complete lock LH	D-36-121	Use tumbler series P-30-161/164
Hyundai	Accent	11/97-99	Complete lock RH	D-36-126	Complete lock LH	D-36-127	Use tumbler series P-30-161/164
Hyundai	Accent	2000-05	Complete lock RH	D-36-140	Complete lock LH	D-36-141	Use tumbler series P-30-161/164
Hyundai	Accent	2006-07	Replacement locks available from Hyundai dealers only				
Hyundai	Azera	2006-07	Replacement locks available from Hyundai dealers only				
Hyundai	Elantra	1992-95	Complete lock RH	D-36-112	Complete lock LH	D-36-113	Use tumbler series P-30-161/164
Hyundai	Elantra	1996 to 3/2/98	Complete lock RH	D-36-122	Complete lock LH	D-36-123	Use tumbler series P-30-161/164
Hyundai	Elantra	3/2/98 – 12/20/98	Complete lock RH	D-36-132	Complete lock LH	D-36-133	Use tumbler series P-30-161/164
Hyundai	Elantra	12/21/98 to 2000	Complete lock RH	D-36-134	Complete lock LH	D-36-135	Use tumbler series P-30-161/164
Hyundai	Elantra	2001-06	Replacement locks available from Hyundai dealers only				
Hyundai	Elantra	2007	Replacement locks available from Hyundai dealers only				
Hyundai	Entourage	2007	Replacement locks available from Hyundai dealers only				
Hyundai	Excel	1986-89	Complete lock RH	D-36-105	Complete lock LH	D-36-106	Use tumbler series P-30-141/144

Check www.carlocks.com for the most up to date information

ASP PART NUMBERING SYSTEM

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)

24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

PART NUMBER LISTING and POPULARITY RATINGS

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com. This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.