

## DOOR LOCKS

Dodge	Colt hatchback & sedan (import)	1985-88	Coded lock without pawl	D-22-109	If original pawl cannot be reused use pawls P-30-322 (RH) or P-30-323 (LH) Use face cap P-30-211 chrome, or P-30-215 black Use tumbler series P-30-141/144		
Dodge	Colt station wagon (import)	1985-90					
Dodge	Colt hatchback & sedan (import)	1989-92	Coded lock without pawl	D-22-110	If original pawl cannot be reused use pawls P-22-303 (RH) or P-22-304 (LH) Use face cap P-30-217 chrome or P-30-218 black Use tumbler series P-30-161/164		
Dodge	Colt hatchback & sedan (import)	1993-96	Complete lock with pawl reversible R&L	D-22-113	Use tumbler series P-33-101/105		
Dodge	Colt Vista (import)	1984-91	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Dodge	Colt Vista (import)	1992-94	Complete lock with pawls RH & LH	D-22-140	Previously available as D-22-120 right side and D-22-121 left side Use tumbler series P-30-161/164		
Dodge	Conquest (import)	1983-89	Lock service package no pawl (without microswitch)	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
			Complete lock RH with microswitch	D-22-103	For LH application use D-22-103 and the original pawl must be reused. Tumblers and face caps same as used with D-22-207 listed above.		
Dodge	Durango	1998-03	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge	Durango	2004-08	Replacement locks available from Strattec or from Chrysler dealers. Use tumbler series P-44-111/114				
Dodge	Daytona (G)	1990-92	Uncoded service pack chrome	DL4815U	Coded pair chrome	DL4815	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Daytona (G)	1993	Uncoded service pack chrome	DL4826U	Coded pair chrome	DL4826	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
			Uncoded service pack black	DL7393U	Coded pair black	DL7393	Use face cap RP6219 (P-44-202) Use tumbler series P-44-101/104
Dodge	Dynasty (CD)	1990-92	Uncoded service pack	DL4815U	Coded pair	DL4815	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Dynasty (CD)	1993	Uncoded service pack	DL4826U	Coded pair	DL4826	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Intrepid (LH)	1993-94	Uncoded service pack	DL4817U	Coded pair	DL4817	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
Dodge	Intrepid (LH)	1995-04	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge	Magnum	2005-08	Remote release only, no lock cylinder.				
Dodge	Monaco	1990-92	Uncoded service pack	D-27-109	Use face cap P-27-201 Use tumbler series P-25-150/180 series		
			Coded pair complete locks with pawls	DP-27-107	NOTE: DP-27-107 cannot be rekeyed to match the original car key.		
Dodge	Neon (PL)	1994-05	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge	Nitro	2007-08	Replacement locks available from Strattec or from Chrysler dealers. Use tumbler series P-44-111/114				
Dodge	Omni (L)	1990	Uncoded service pack	DL4815U	Coded pair	DL4815	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Raider (import)	1987-89	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Dodge	Ramcharger	1990-92	Uncoded service pack	DL4815U	Coded pair	DL4815	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Ramcharger	1993	Uncoded service pack	DL4826U	Coded pair	DL4826	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Dodge	Ram Charger	1999-04	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge	Shadow (P)	1990-92	Uncoded service pack chrome	DL4816U	Coded pair chrome	DL4816	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack Black	DL4822U	Coded pair black	DL4822	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Dodge	Shadow (P)	1993-94	Uncoded service pack chrome	DL4817U	Coded pair chrome	DL4817	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack Black	DL4823U	Coded pair black	DL4823	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Dodge	Spirit (A)	1989-92	Uncoded service pack chrome	DL4816U	Coded pair chrome	DL4816	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack Black	DL4822U	Coded pair black	DL4822	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Dodge	Spirit (A)	1993-94	Uncoded service pack chrome	DL4817U	Coded pair chrome	DL4817	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack Black	DL4823U	Coded pair black	DL4823	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104

## DOOR LOCKS

Dodge Van	Caravan	1995	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge Van	Caravan	1996-00	Uncoded service pack	D-44-019	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114		
Dodge Van	Caravan	2001-07	Uncoded service pack	DL6847U	Coded pair	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
Dodge Van	Ram Van	1994	Uncoded service pack	DL4826U	Coded pair	DL4826	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
			Uncoded service pack	DL7393U	Coded pair	DL7393	Use face cap RP6219 (P-44-202) Use tumbler series P-44-101/104
Dodge Van	Ram Van	1995-04	Uncoded service pack chrome	DL6946U	Coded pair chrome	DL6946	Use face cap RP6218 (P-44-201) Use tumbler series P-44-111/114
			Uncoded service pack black	DL6948U	Coded pair black	DL6948	Use face cap RP6219 (P-44-202) Use tumbler series P-44-111/114
Dodge Van	Sprinter	2003-06	Uncoded plug	D-21-102	Use tumbler series P-21-191/194		
Dodge Van	Sprinter	2007-08	Replacement locks available from Freightliner, Dodge, or Mercedes-Benz dealers only				
Eagle	All - 4WD wagon & sedan	1981-88	Uncoded service pack including pawl (R&L)	D-43-203	Coded pair	DP-43-103	Use tumbler series P-43-101/115
Eagle	Medallion sedan	All	Uncoded service pack	D-27-109	Use face cap P-27-201 Use tumbler series P-25-150/180 series		
			Coded pair complete locks with pawls	DP-27-107	NOTE: DP-27-107 cannot be rekeyed to match the original car key.		
Eagle	Medallion station wagon	All	Uncoded service pack with pawl RH & LH	D-27-207	Use tumbler series P-25-250/281 series		
			Coded pair complete locks with pawls	DP-27-107	Use tumbler series P-25-250/281 series		
Eagle	Premier	1988-91	Uncoded service pack	D-27-109	Use face cap P-27-201 Use tumbler series P-25-150/180 series		
			Coded pair complete locks with pawls	DP-27-107	NOTE: DP-27-107 cannot be rekeyed to match the original car key.		
Eagle	Summit	1989-92	Coded lock without pawl	D-22-110	If original pawl cannot be reused use pawls P-22-303 (RH) or P-22-304 (LH) Use face cap P-30-217 chrome or P-30-218 black Use tumbler series P-30-161/164		
Eagle	Summit	1993-96	Complete lock with pawl reversible R&L	D-22-113	Use tumbler series P-33-101/105		
Eagle	Summit Wagon (Colt Vista)	1984-91	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Eagle	Summit Wagon (Colt Vista)	1992-94	Complete lock with pawls RH & LH	D-22-140	Previously available as D-22-120 right side or D-22-121 left side Use tumbler series P-30-161/164		
Eagle	Talon	1990-94	Complete lock RH	D-22-111	Complete lock LH	D-22-112	Use tumbler series P-30-161/164
Eagle	Talon	1995-99	Coded lock without pawl	D-22-230	Previously available as complete locks D-22-130 (RH) and D-22-131 (LH) If original pawl cannot be reused, use P-22-306 (RH) or P-22-307 (LH) Use tumbler series P-30-161/164		
Eagle	Vision (LH)	1993-94	Uncoded service pack chrome	DL4817U	Coded pair chrome	DL4817	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack black	DL4823U	Coded pair black	DL4823	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Eagle	Vision (LH)	1995-98	Uncoded service pack chrome	DL6847U	Coded pair chrome	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
			Uncoded service pack black	DL6846U	Coded pair black	DL6846	Use face cap RP6220 (P-44-204) Use tumbler series P-44-111/114
Eagle Truck	Heavy truck	All	See the Heavy Truck section				
Edsel	All	1958-59	Coded lock RH without pawl	D-42-170	Coded lock LH without pawl	D-42-171	Coded pair available: DP-42-170 The original pawls must be reused Use tumbler series P-42-181/185
Edsel	All	1960	No longer available – try classic Edsel / Ford parts specialists Use tumbler series P-42-181/185				
Fargo	All	All	See Dodge Pickup or Dodge Van				
Ferrari	All	All	See the Exotic Brands section				
Fiat	124 sedan	to 1970	Coded plug	D-17-511	Available only with FT37 / FA1 / F79-1 / AF7A keyway Use tumbler series P-17-121/123		
Fiat	124 sedan	1971-up	Complete lock and handle RH	D-17-101	Complete lock and handle LH	D-17-102	Use tumbler series P-17-121/123
			Uncoded plug uses FT37 key	D-17-201	Uncoded plug uses FT38 key	D-17-301	Use tumbler series P-17-121/123
Fiat	124 Spyder	1971-up	Replacement locks no longer available - try classic Fiat parts specialists Use tumbler series P-17-111/113				
Fiat	124 wagon	to 1972	Coded plug	D-17-511	Available only with FT37 / FA1 / F79-1 / AF7A keyway Use tumbler series P-17-121/123		
Fiat	124 wagon	1973-up	see Fiat 124 sedan 1971-up				
Fiat	128 sedan	All	Uncoded plug uses FT37 key	D-17-201	Uncoded plug uses FT38 key	D-17-301	Use tumbler series P-17-121/123
Fiat	131 Mirafiori, Brava	1975-81	Uncoded plug uses FT37 key	D-17-202	Use tumbler series P-17-121/123		

## DOOR LOCKS

Merkur	Scorpio	1988-89	Uncoded service pack RH	D-18-033	Uncoded service pack LH	D-18-034	Tumblers included in uncoded service pack. Tumblers also available separately: P-18-121/124
MG	MGB	1962-65	Coded pair 1.2 inch diameter lock	DP-14-242	On some cars the original pawls must be reused. Use tumbler series P-14-211/213		
MG	MGB, Midget	1966-up	Complete lock with pawl reversible R&L FT code series (62FTkey blank)	D-14-213	Coded pair with pawls FT code series (62FT key blank)	DP-14-213	NOTE: Locks using FS code series (62FS key blank) previously available as D-14-211 / DP-14-211 are discontinued when out. Tumblers (FS) - P-14-201/203 Tumblers (FT) – P-14-211/213
Mini	All	before 2000	see Austin Mini				
Mini	Cooper	2002-08	Replacement locks available from Mini dealers only Use tumbler series P-31-171/175				
Mitsubishi	3000GT	1990-94	Complete lock RH	D-22-132	Complete lock LH	D-22-133	For cars with factory alarm switch the original switch must be reused. Use tumbler series P-30-161/164
Mitsubishi	3000GT	1995-96	Complete lock RH without factory alarm	D-22-132	Complete lock LH without factory alarm	D-22-133	Use tumbler series P-30-161/164
			Complete lock RH with switch for alarm	D-22-134	Complete lock LH with switch for alarm	D-22-135	
Mitsubishi	Cordia	1983-86	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Mitsubishi	Diamante sedan	1992-96	Complete lock RH microswitch on pawl	D-22-128	Complete lock LH microswitch on pawl	D-22-129	Use tumbler series P-30-161/164
			Coded lock R&L, no microswitch on pawl	D-22-122	Use tumbler series P-30-161/164		
Mitsubishi	Diamante wagon	1992-97	see Diamante sedan 1992-96				
Mitsubishi	Diamante sedan	1997-04	Complete lock with pawl reversible R&L	D-22-136	Use tumbler series P-30-161/164		
Mitsubishi	Eclipse	1990-94	Complete lock RH	D-22-111	Complete lock LH	D-22-112	Use tumbler series P-30-161/164
Mitsubishi	Eclipse	1995-99	Coded lock without pawl	D-22-230	Previously available as complete locks D-22-130 (RH) and D-22-131 (LH) If original pawl cannot be reused, use P-22-306 (RH) or P-22-307 (LH) Use tumbler series P-30-161/164		
Mitsubishi	Eclipse	2000-05	Replacement locks available from Strattec or Mitsubishi dealers.				
Mitsubishi	Eclipse	2006-07	Replacement locks available from Strattec or Mitsubishi dealers.				
Mitsubishi	Endeavor	2004-07	Replacement locks available from Strattec or Mitsubishi dealers.				
Mitsubishi	Evolution	2003-06	see Lancer 2002-06				
Mitsubishi	Expo	1992-96	Complete lock with pawls RH & LH	D-22-140	Previously available as D-22-120 right side and D-22-121 left side Use tumbler series P-30-161/164		
Mitsubishi	Galant	1985-86	Coded lock	D-22-108	If original pawl cannot be reused, use P-22-303 (RH) or P-22-304 (LH) Use tumbler series P-30-141/144		
Mitsubishi	Galant	1987	Complete lock RH	D-22-126	Complete lock LH	D-22-127	Use tumbler series P-30-141/144
Mitsubishi	Galant	1988-93	Coded lock for cars without microswitch	D-22-110	If original pawl cannot be reused, use P-22-303 (RH) or P-22-304 (LH) Use face cap P-30-217 Use tumbler series P-30-161/164		
			Coded lock design to clip a switch on back (switch not included)	D-22-114			
Mitsubishi	Galant	1994-98	Complete lock with pawls RH & LH	D-22-140	Previously available as D-22-120 right side and D-22-121 left side Use tumbler series P-30-161/164		
Mitsubishi	Galant	1999-03	Replacement locks available from Strattec or Mitsubishi dealers				
Mitsubishi	Galant	2004-07	Replacement locks available from Strattec or Mitsubishi dealers				
Mitsubishi	Lancer	2002-06	Complete lock RH	D-22-138	Complete lock LH	D-22-139	Use tumbler series P-20-131/155
Mitsubishi	Mirage except station wagon	1985-88	Coded lock	D-22-109	If original pawl cannot be reused, use P-22-322 (RH) or P-22-323 (LH) Use face cap P-30-211 (chrome) or P-30-215 (black) Use tumbler series P-30-141/144		
Mitsubishi	Mirage wagon	1985-90					
Mitsubishi	Mirage	1989-92	Coded lock	D-22-110	If original pawl cannot be reused, use P-22-303 (RH) or P-22-304 (LH) Use face cap P-30-217 (chrome) or P-30-218 (black) Use tumbler series P-30-161/164		
Mitsubishi	Mirage	1993-96	Complete lock with pawl reversible R&L	D-22-113	Use tumbler series P-33-101/105		
Mitsubishi	Mirage	1997-02	Complete lock with pawl reversible R&L	D-22-115	Use tumbler series P-33-101/105		
Mitsubishi	Montero	1983-91	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Mitsubishi	Montero	1992-00	Coded lock for cars without microswitch	D-22-110	If original pawl cannot be reused, use pawls as follows: bent pawls - P-22-312 (RH) or P-22-313 (LH) – usually with D-22-110 straight pawl – P-30-329 - usually with D-22-114 Use face cap P-30-217 (chrome) or P-30-218 (black) Use tumbler series P-30-161/164		
			Coded lock design to clip a switch on back (switch not included)	D-22-114			

## DOOR LOCKS

Opel (Japan)	All	1976-79	Uncoded service pack	D-24-201	Use reversible pawl P-30-310 for RH and LH Use face cap P-24-203 (chrome) or P-24-204 (black) Use tumbler series P-30-141/144		
Pantera	All	All	See the Exotic Brands section				
Panther	All	All	See the Exotic Brands section				
Peterbilt	All	All	See the Heavy Truck section				
Peugeot	304, 504	All	Complete lock with reversible pawl R/L	D-25-101	Use tumbler series P-25-100/109		
Peugeot	405	All	Uncoded service pack RH	D-25-208	Uncoded service pack LH	D-25-209	Use tumbler series P-25-250/281
Peugeot	505	1980- 3/84	Complete lock with reversible pawl R/L	D-25-102	Use tumbler series P-25-150/180 series		
Peugeot	505	6/84-92	Uncoded service pack RH	D-25-206	Uncoded service pack LH	D-25-207	Use tumbler series P-25-250/281
Peugeot	604	6/77-6/79	Coded pair R+L including pawls	DP-25-106	Use tumbler series P-25-150/180		
Peugeot	604	7/79-up	Coded pair R+L including pawls	DP-25-107	Use tumbler series P-25-150/180		
Plymouth	All	to 1965	No longer available, try classic Chrysler / MOPAR parts specialists				
Plymouth	All exc. imports exc. lighted exc. Acclaim 89	1966-89	Uncoded lock with pawl reversible R&L	DL1502U	Coded pair with pawls	DL1502	NOTE: DL1502 will use a different keyway than original on pre-1968. Use tumbler series P-44-121/126
	Lighted keyhole black	1970-89	Uncoded lock with pawl reversible R&L	DL1534U	Use tumbler series P-44-121/126		
	Lighted keyhole chrome	1970-89	Previously sold as DL1533, discontinued when out Use tumbler series P-44-121/126				
Plymouth	Acclaim (A)	1989-92	Uncoded service pack chrome	DL4816U	Coded pair chrome	DL4816	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack black	DL4822U	Coded pair black	DL4822	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Plymouth	Acclaim (A)	1993-94	Uncoded service pack chrome	DL4817U	Coded pair chrome	DL4817	Use face cap RP6215 (P-44-203) Use tumbler series P-44-101/104
			Uncoded service pack black	DL4823U	Coded pair black	DL4823	Use face cap RP6220 (P-44-204) Use tumbler series P-44-101/104
Plymouth	Acclaim (A)	1995	Uncoded service pack chrome	DL6847U	Coded pair chrome	DL6847	Use face cap RP6215 (P-44-203) Use tumbler series P-44-111/114
			Uncoded service pack black	DL6846U	Coded pair black	DL6846	Use face cap RP6220 (P-44-204) Use tumbler series P-44-111/114
Plymouth	Arrow (Import)	1976-80	Coded lock without pawl	D-22-106	If original pawl cannot be reused use pawl P-30-301, reversible RH & LH Use face cap P-30-201 Use tumbler series P-30-141/144		
Plymouth	Breeze (JA)	1995-00	Uncoded service pack chrome	DL6946U	Coded pair chrome	DL6946	Use face cap RP6218 (P-44-201) Use tumbler series P-44-111/114
			Uncoded service pack black	DL6948U	Coded pair black	DL6948	Use face cap RP6219 (P-44-202) Use tumbler series P-44-111/114
Plymouth	Colt hatchback (import)	1979-84	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Plymouth	Colt hatchback & sedan (import)	1985-88	Coded lock without pawl	D-22-109	If original pawl cannot be reused, use P-22-322 (RH) or P-22-323 (LH) Use face cap P-30-211 (chrome) or P-30-215 (black) Use tumbler series P-30-141/144		
Plymouth	Colt station wagon (import)	1985-90					
Plymouth	Colt hatchback & sedan (import)	1989-92	Coded lock without pawl	D-22-110	If original pawl cannot be reused use pawls P-22-303 (RH) or P-22-304 (LH) Use face cap P-30-217 chrome or P-30-218 black Use tumbler series P-30-161/164		
Plymouth	Colt hatchback & sedan (import)	1993-96	Complete lock with pawl reversible R&L	D-22-113	Use tumbler series P-33-101/105		
Plymouth	Colt Vista (import)	1984-91	Lock service package no pawl	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
Plymouth	Colt Vista (import)	1992-94	Complete lock with pawls RH & LH	D-22-140	Previously available as D-22-120 right side and D-22-121 left side Use tumbler series P-30-161/164		
Plymouth	Conquest (import)	1983-89	Lock service package no pawl (without microswitch)	D-22-207	Previously available as D-22-107 or D-22-105 complete locks If original pawl cannot be reused use pawls P-22-301 (RH) or P-22-302 (LH) Use face cap P-22-201 chrome, or P-22-202 black Use tumbler series P-30-141/144		
			Complete lock RH with microswitch	D-22-103			
Plymouth	Cricket (import)	1971-73	Try classic Chrysler parts suppliers or classic British car parts suppliers.				
Plymouth	Horizon (L)	1990	Uncoded service pack chrome	DL4815U	Coded pair chrome	DL4815	Use face cap RP6218 (P-44-201) Use tumbler series P-44-101/104
Plymouth	Laser (import)	1990-94	Complete lock RH	D-22-111	Complete lock LH	D-22-112	Use tumbler series P-30-161/164

## ASP PART NUMBERING SYSTEM

### The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)

24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.



## ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

**Audi** - also found on some Porsche and Volkswagen

**Ford USA** – also found on some Mazda and Nissan

**Honda / Acura** - also found on some Isuzu

**Mazda** – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

**Nissan** - also found on some Subaru and Isuzu truck

**Toyota** – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

**Volkswagen** - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

**British cars** - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

**French cars** - Peugeot, Renault, Citroen

**German cars** - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

**Italian cars** - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

## Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

## PART NUMBER LISTING and POPULARITY RATINGS

### Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

**A** = Most popular items (lock cylinders and replacement parts)

**B** = Second most popular group of lock cylinders

**Y** = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

**C** = Third most popular group of lock cylinders

**Z** = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

**H** = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

**S** = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

**DWO** = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check [www.carlocks.com](http://www.carlocks.com) for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on [www.carlocks.com](http://www.carlocks.com). This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

### Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.