

ATLAS SOUND RELEASES A NEWLY DESIGNED FLUSH/SURFACE MOUNTED 2RU/3RU WALL MOUNTED TILT OUT RACK

AWR2W & AWR3W

Convenient access and lock-in security highlights Atlas-Sound's re-designed AWR2W – 2RU and AWR3W – 3RU tilt-out wall cabinets for 19" equipment. This re-designed welded model can be surface or recessed mounted (trim ring included) and includes a 3RU panel opening above the main bay for connector panels or power distribution. These cabinets are perfect for mounting remote amplifiers and control equipment.

The series features a 16-ga. CRS formed door frame with a 16-ga. CRS locking tilt-out door which closes against rack face plate. The surface mounting door is attached to the frame internally with two pin style hinges to prevent tampering.

Doors can be opened to two positions—tilt-out for operation and by releasing side catches, the door will open to approximately 90° for equipment installation and maintenance. Units are furnished with two steel safety catch cables which suspend and hold doors at 90°.

Front panels have 45-degree mitered edges to present a clean flush appearance. Back box is 16-ga. CRS equipped with six concentric knockouts of 1/2" and 3/4". AWR Series is shipped complete and ready for installation. Panel mounting holes accept 10-32 hardware.



MODEL	Rack Space	Usable Depth	Mounting Depth	Height	Width	Depth	Weight
AWR2W	2	20" Top RU 17.25" Bottom RU	4"	34"	27"	4.8"	54 lbs
AWR3W	3	20" Top RU 17.25" Bottom RU	5.75"	34"	27"	6.55"	57 lbs

