

FB4CPB

Features

- 16GU Construction
- Durable Galvanized Steel Construction
- Four Compound Combination Knockouts ($\frac{1}{2}$ " - $\frac{3}{4}$ ", 13 - 19mm)
- Unpainted Finish

Specifications

| | |
|-----------------|---------------------------|
| Height | 6 $\frac{1}{8}$ " (156mm) |
| Width | 6 $\frac{1}{8}$ " (156mm) |
| Depth | 4" (101.6mm) |
| Shipping Weight | 4.00 lbs (1.81 kgs) |



HXLP-3-12

Features

- A3M or Equal
- Cable Connector
- Male 3 Conductor

Specifications

| | |
|-----------------|---------------------|
| Connector Type | A3M |
| Shipping Weight | 0.22 lbs (0.10 kgs) |



HXLP-3-11

Features

- A3F or Equal
- Cable Connector
- Female 3 Conductor

Specifications

| | |
|-----------------|---------------------|
| Connector Type | A3F |
| Shipping Weight | 0.50 lbs (0.23 kgs) |



SG-XLR-F1

Features

- Female 3 Conductor
- Perfect for Remote Microphone Applications
- Wall / Panel Receptacle

Specifications

| | |
|-----------------|-----------------------------|
| Height | 4 $\frac{3}{4}$ " (121mm) |
| Width | 2 $\frac{15}{16}$ " (532mm) |
| Shipping Weight | 0.50 lbs (0.23 kgs) |

