

Advantage Line Quick Selection Guide - Public Address

Volume Controls



► Volume Controls

LBC1400/10

LBC1401/10

LBC1410/10

LBC1411/10

LBC1420/10

Dim	87 x 87 mm	81 x 81 mm	87 x 87 mm	81 x 81 mm	87 x 147 x 61.5 mm
Weight	226 g	214 g	226 g	214 g	512 g
Mounting	MK	U40	MK	U40	MK D/E2
Input Voltage	100 V	100 V	100 V	100 V	100 V
Power	12 W (max)	12 W (max)	36 W (max)	36 W (max)	100 W (max)
Attenuation Steps	5 x 3 dB + off	5 x 3 dB + off	8 x 3 dB + off	8 x 3 dB + off	10 x 2 dB + off
Frequency Response	50 Hz to 20 kHz	50 Hz to 20 kHz	50 Hz to 20 kHz	50 Hz to 20 kHz	50 Hz to 20 kHz
THD	< 0.5%	< 0.5%	< 0.5%	< 0.5%	< 0.5%
Current Consumption	20 mA @ 24 V DC	20 mA @ 24 V DC	20 mA @ 24 V DC	20 mA @ 24 V DC	20 mA @ 24 V DC
Connection	Screw terminals	Screw terminals	Screw terminals	Screw terminals	Screw terminals
Color	White (RAL 9010)	White (RAL 9010)	White (RAL 9010)	White (RAL 9010)	White (RAL 9010)