




.050 PUSH PLATES



NUMBER	DIMENSIONS	ANSI A156.6	MATERIAL
69	3" X 12"	J301	Aluminum, Brass, Bronze, Stainless Steel, Plastic
70	3 1/2" X 15"	J301	
71	4" X 16"	J301	
72	6" X 16"	J301	
73	8" X 16"	J301	

SHELF PACK: 10

Box Pack

FASTENERS: #6 x 5/8 OH SMS

FEATURE: Four beveled edges


FINISHES: 605, 606, 609, 612, 613, 619, 620, 626, 628, 629, 630

ORDERING: Specify plate number followed by size and finish –
specify additional options and/or features.

OPTIONS:

- Rounded corners - RC
- Custom sizes available
- Torx screws
- Scotch Mount, double face tape (no holes, no screws)
- Magnetic, no holes, no screws
- Hole cut outs available

.125 PUSH PLATES



NUMBER	DIMENSIONS	ANSI A156.6	MATERIAL
76	3" X 12"	J301	Stainless Steel
77	3 1/2" X 15"	J301	
78	4" X 16"	J301	
79	6" X 16"	J301	
80	8" X 16"	J301	

SHELF PACK: 10

Box Pack

FASTENERS: #6 x 5/8 OH SMS

FEATURE: Four beveled edges

FINISH: 630

ORDERING: Specify plate number followed by size and finish –
specify additional options and/or features.

OPTIONS:

- Rounded corners - RC
- Custom sizes available
- Torx screws
- Scotch Mount, double face tape (no holes, no screws)
- Magnetic, no holes, no screws
- Hole cut outs available