



WROUGHT WALL BUMPERS



I400



I402



I406



I407

NUMBER	TYPE	PROJ.	DIA.	ANSI A156.16	MATERIAL
I400	Convex	1/2"	1"	L02101	Brass
I402	Concave	1 1/8"	1 1/2"	—	Solid Brass
I406	Convex	1 1/8"	2 1/2"	L22101, L52101	Wrought
I407	Concave	1"	2 1/2"	L22251, L52251	Wrought

SHELF PACK: (I400, I406, I407) 50 Polybagged
(I402) 10

FASTENERS: (I400) 1 ea. #8 x 1" SMS, 1 ea. Brad Nail, 1 ea. Plastic Anchor
(I402) 1 ea. #10 x 1 1/4" SMS, 1 ea. Plastic Anchor &
Plastic Drywall Anchor
(I406, I407) 1 ea. #8 x 1 1/4" SMS, 1 ea. Plastic Anchor &
Plastic Drywall Anchor

FINISHES: (I400) 605, 606, 613, 625, 626
(I402) 626
(I406) 605, 606, 612, 613, 619, 620, 625, 626, 630
(I407) 605, 606, 612, 613, 619, 620, 625, 626, 630

CAST WALL BUMPERS



I412



I413



I410

NUMBER	TYPE	PROJ.	DIA.	ANSI A156.16	MATERIAL
I410	Convex	7/8"	3 7/8"	—	Cast Brass
I412	Convex	1"	2 1/2"	L12101	Cast Brass
I413	Concave	1"	2 1/2"	L12251	Cast Brass

SHELF PACK: 10 Polybagged

FASTENERS: (I412, I413) 1 ea. #10 x 1 1/4" SMS, 1 ea. Plastic Anchor &
Plastic Drywall Anchor
(I410) 1 ea. 1/4-20 x 1 1/4" MS, 3 ea. #8-32 x 1/4" MS, 1 ea.
Lead Expansion Shield

FINISHES: (I412, I413) 605, 606, 613, 626
(I410) 626

OPTIONS: (I410) Torx screws available

RUBBER WALL BUMPERS



I401

NUMBER	TYPE	PROJ.	DIA.	MATERIAL
I401	Concave	9/16"	1 13/16"	Rubber

SHELF PACK: 10 Polybagged

FASTENER: Adhesive

FINISHES: White & Gray

Proj. = Projection, Dia. = Diameter