

D200 Series lock features

**Thumbturn
(Inside only)**

Deadbolt thrown or retracted by turn unit only. No outside trim. Bolt automatically deadlocks when fully thrown.

ANSI/BHMA E0192



D261

**Thumbturn
(Inside with occupancy indicator)**

Deadbolt thrown or retracted by turn unit only. Occupancy indicator on outside (reads either in use or vacant with color coding). Bolt automatically deadlocks when fully thrown.

Emergency key supplied.



D271

**Thumbturn
(Inside with blank rose)**

Deadbolt thrown or retracted by turn unit only. Outside blank rose. Bolt automatically deadlocks when fully thrown.

ANSI/BHMA E01112



D261M

Lock type comparison chart
Glossary and finish chart
MA Series
RU Series
T Series
X Series
K Series
B Series
W Series
H2 Series
D Series
K900 Series
Construction keying and product ID chart

Function cross-reference

Mounting screws

Part number	Specify finish	Description	Application		
		Size	Type	Use	Door thickness
Keyed, single conventional cylinder					
B600-100		1/4"-28 x 1 ¹⁵ / ₁₆ "	POH mach.	Mounting	1 ³ / ₈ " - 1 ³ / ₄ "
B600-101		1/4"-28 x 1 ¹⁵ / ₁₆ "	POH mach.	Mounting	1 ³ / ₈ " - 2 ¹ / ₄ "
B600-066		6-32 x 1/4"	PH mach.	Turn	-
B520-298		10-32 x 3/8"	PH mach.	Anti-pry shield	-
Keyed, single SFIC cylinder					
B600-100		1/4"-28 x 1 ¹⁵ / ₁₆ "	POH mach.	Mounting	1 ³ / ₈ " - 2 ¹ / ₄ "
B600-066		6-32 x 1/4"	PH mach.	Turn	-
Keyed, double conventional cylinder					
B600-047		1/4"-28 x 3 ¹³ / ₁₆ "	PH mach.	Mounting	1 ³ / ₈ " - 1 ³ / ₄ "
B600-078		1/4"-28 x 1 ²⁹ / ₆₄ "	PH mach.	Mounting	1 ³ / ₈ " - 2 ¹ / ₄ "
B520-298		10-32 x 3/8"	PH mach.	Anti-pry shield	-
Keyed, double SFIC cylinder					
B600-053		1/4"-28 x 3 ⁶¹ / ₆₄ "	PH mach.	Mounting	1 ³ / ₈ " - 2 ¹ / ₄ "
B520-298		10-32 x 3/8"	PH mach.	Anti-pry shield	-
Keyless, D261					
B600-066		6-32 x 1/4"	PH mach.	Turn	-
B600-048		10-32 x 1/2"	PH mach.	Mounting plate	-
F506-359		#8 x 3/4"	RH wood	Mounting plate	
Keyless, D261M, D271					
B520-662		10-32 x 1 ³ / ₄ "	POH mach.	Mounting	-
B520-663		10-32 x 1 ³ / ₄ "	POH mach.	Mounting	-
B600-066		6-32 x 1/4"	PH mach.	Turn	
All functions					
C603-897		#8 x 3/4"	PFH combo.	Deadbolt & strike	-
J520-028		#8 x 2"	PFH wood	2" strike screw	-
R525-256		#12 x 3"	PFH wood	3" metal dust box	-