Accessories

| ltem | Accessory | Description |
|------|--|--|
| | 2001M: Plug-in bridge rectifier | Converts AC to unfiltered DC. Rated 35 V, 1 Amp Includes MOV and self-resettable fuse Not recommended for 1006 Electric Strike |
| | 2001-1: Wire-in bridge rectifier | Converts AC to unfiltered DC. Rated 35 V, 2 Amp Not recommended for 1006 Electric Strike |
| | 2004M: ElectroLynx® adapter | Adapter between existing HES electric strikes and ElectroLynx® connectors |
| | 2005M3: SMART Pac [®] III | In-line power controller able to receive input voltages from 12-32V AC or DC. Built-in bridge rectifier. Reduces initial voltage by 25% to extend the life of the electric strike. Includes built-in resettable fuse, MOV, voltage regulation and input voltage level indicating and unit status For use with 1006, input voltage must be DC |
| | 2006M: Plug-in buzzer | Audible operation indicator. At 24 VDC, 75db at 11-3/4" |
| | 2007M: Plug-in pigtail connectors | With 4" wire leads |
| H OS | 150: Strike latch guard | Stainless steel. Installed at the edge of the door to cover the lock and electric strike |