

Tubular Duplicat™

Long-Lasting Motor

High-Quality Carbide Cutter

Duplicates 7-Pin Standard Sized Tubular Keys

Duplicates keys with any space and depth configurations.

1

Tubular Duplicat™
No. 747E
No. 747E240V (240 volt)

Able to Duplicate from an HPC Tubular Pick

This machine can duplicate 7-pin Standard Tubular Keys.

The **HPC/Scotsman Tubular Duplicat™** is a standard tubular key duplicator. **It duplicates 7-pin standard sized tubular keys** with spaces in any position and cuts of any depth. The machine is equipped with a carbide cutter for smooth cutting and a plexiglas shield for added safety. It also can duplicate a key from an HPC Tubular Pick. The Tubular Duplicat™ provides an **economical key cutting solution** for standard sized tubular keys.

Tubular Duplicat™ No. 747E

115VAC 60hz, 1/15 hp 1.5 amps
Shipping Weight: 11 lbs (5 kg)
Machine Size: 16"W x 5"D x 5"H (41W x 13D x 13H cm)
Bench Size: 20"W x 6"D (51W x 15D cm)

No. 747E240V

240VAC 50hz, 1/10 hp 1.2 amp
Shipping Weight: 11 lbs (5 kg)
Machine Size: 16"W x 5"D x 5"H (41W x 13D x 13H cm)
Bench Size: 20"W x 6"D (51W x 15D cm)

KEY MACHINES

Pocket Cut-Up™



SPACE SAVER



Pocket Cut-Up™ No. TKM-90

Shipping Weight: 0.8 lbs / 0.4 kg
Machine Size: 2" dia. x 4" long
5 dia. x 10 long cm

The **Pocket Cut-Up™** is a compact, portable tubular key machine. It is factory preset to cut **7-pin standard, center sequence tubular keys by code**. Offset left and offset right sequence (including dead pin cuts) can be cut with one simple adjustment. **It also cuts Greenwald style tubular keys**. The tubular key blank is held firmly in place by the swing-away key holding fixture, that locks the depth adjustment knob at pre-selected depths. By turning the knob, the carbide cutter cuts brass and steel key blanks with ease. The Pocket Cut-Up™ is so **incredibly lightweight and compact** that it can be carried in your pocket!

Tubular Key Blanks



No. 137 (Steel)
50 per box
All Steel Construction with Nickel Plating (standard size)
.375"/9.53mm OD
.312"/7.92mm ID



No. 137B (Brass)
50 per box
Unplated Brass Body with Nickel Plated Steel Head (standard size)
.375"/9.53mm OD
.312"/7.92mm ID



No. 137SB (Brass)
50 per box
Unplated Brass Body with Nickel Plated Steel Head (small bore)
.365"/9.27mm OD
.300"/7.62mm ID