

Black & Gold HSS Fractional 3/8" Reduced Shank Jobber Length Drill Bits with 135° Split Point (Series 30191)



3019128B

- Standard Black & Gold bit with 3/8" reduced shank

Set:

Metal Index: 3018005

Black Oxide HSS Fractional Straight Shank Jobber Length Drill Bits with 135° Split Point (Series 675/635)



63524ZR

- 135° split-point tip starts drilling immediately and eliminates "walking."
- Manufactured with premium high speed steel with black oxide coating for corrosion resistance.
- Straight shank

Set:

Pro Set Cases: 314015

Black Oxide HSS Fractional 3/8" Reduced Shank Jobber Length Drill Bits with 135° Split Point (Series 678/634)



63432

- Standard Black Oxide bit with 3/8" reduced shank

Sets:

Pro Set Case: 314018

Metal Index: 3018004

Size	Decimal Equiv.	Flute Length	Overall Length	Carded Item #	Bulk Item #
25/64"	.3906	3-3/4"	5-1/8"	—	3019125B
13/32"	.4063	3-7/8"	5-1/4"	—	3019126B
27/64"	.4219	3-15/16"	5-3/8"	—	3019127B
7/16"	.4375	4-1/16"	5-1/2"	—	3019128B
29/64"	.4531	4-3/16"	5-5/8"	—	3019129B
15/32"	.4688	4-5/16"	5-3/4"	—	3019130B
31/64"	.4844	4-3/8"	5-7/8"	—	3019131B
1/2"	.5000	4-1/2"	6"	—	3019132B

Size	Decimal Equiv.	Flute Length	Overall Length	Carded Item #	Bulk Item #
3/64"	.0469	3/4"	1-3/4"	—	63503
1/16"	.0625	7/8"	1-7/8"	67504*	63504
5/64"	.0781	1"	2"	67505*	63505
3/32"	.0938	1-1/8"	2-1/4"	67506*	63506
7/64"	.1094	1-1/2"	2-5/8"	67507*	63507
1/8"	.1250	1-5/8"	2-3/4"	67508*	63508
9/64"	.1406	1-3/4"	2-7/8"	67509	63509
5/32"	.1563	2"	3-1/8"	67510	63510
11/64"	.1719	2-1/8"	3-1/4"	67511	63511
3/16"	.1875	2-5/16"	3-1/2"	67512	63512
13/64"	.2031	2-7/16"	3-5/8"	67513	63513
7/32"	.2188	2-1/2"	3-3/4"	67514	63514
15/64"	.2344	2-5/8"	3-7/8"	67515	63515
1/4"	.2500	2-3/4"	4"	67516	63516
17/64"	.2656	2-7/8"	4-1/8"	67517	63517
9/32"	.2813	2-15/16"	4-1/4"	67518	63518
19/64"	.2969	3-1/16"	4-3/8"	67519	63519
5/16"	.3125	3-3/16"	4-1/2"	67520	63520ZR
21/64"	.3281	3-5/16"	4-5/8"	67521	63521ZR
11/32"	.3438	3-7/16"	4-3/4"	67522	63522ZR
23/64"	.3594	3-1/2"	4-7/8"	67523	63523ZR
3/8"	.3750	3-5/8"	5"	67524	63524ZR
25/64"	.3906	3-3/4"	5-1/8"	67525	63525ZR
13/32"	.4063	3-7/8"	5-1/4"	67526	63526ZR
27/64"	.4219	3-15/16"	5-3/8"	67527	63527ZR
7/16"	.4375	4-1/16"	5-1/2"	67528	63528ZR
29/64"	.4531	4-3/16"	5-5/8"	67529	63529ZR
15/32"	.4688	4-5/16"	5-3/4"	67530	63530
31/64"	.4844	4-3/8"	5-7/8"	67531	63531
1/2"	.5000	4-1/2"	6"	67532	63532

*Note: 2 bits per Card

Size	Decimal Equiv.	Flute Length	Overall Length	Carded Item #	Bulk Item #
25/64"	.3906	3-3/4"	5-1/8"	67825	63425
13/32"	.4063	3-7/8"	5-1/4"	67826	63426
27/64"	.4219	3-15/16"	5-3/8"	67827	63427
7/16"	.4375	4-1/16"	5-1/2"	67828	63428
29/64"	.4531	4-3/16"	5-5/8"	67829	63429
15/32"	.4688	4-5/16"	5-3/4"	67830	63430
31/64"	.4844	4-3/8"	5-7/8"	67831	63431
1/2"	.5000	4-1/2"	6"	67832	63432

Pro Set Cases



314018



318015



316015



4935643



3018009

Description	Type	Contents	Point	Finish	Item #
15-Piece Set	Black Oxide HSS Fractional Straight Shank Jobber Length	1/16" - 3/8"	135°	Black Oxide	314015
18-Piece Set	Black Oxide HSS Fractional Jobber Length	1/16" - 1/2" with 3/8" Reduced Shank	135°	Black Oxide	314018
20-Piece Set	Drill/Drive Set with Black Oxide HSS Drills and Screwdriver Bits	1/16" (2), 3/32", 1/8" (2), 5/32", 3/16", 1/4" Drills and 12 Screwdriver and Nutdriver Bits	135°	Black Oxide	357020
15-Piece Set	Cobalt HSS Fractional Straight Shank Jobber Length	1/16" - 3/8"	135°	Cobalt	316015
15-Piece Set	TURBOMAX® HSS Fractional Straight Shank Jobber	Length 1/16"-3/8"	TURBOMAX	Black & Gold Oxide	318015
18-Piece Set	TURBOMAX HSS Fractional Jobber	Length 1/16"-1/2" with 3/8" Reduced Shank	TURBOMAX	Black & Gold Oxide	3018024SM
12-Piece Set	Black Oxide HSS 1/4" Hex Shank Jobber Length	1/16", 5/64", 3/32", 7/64", 1/8" (2), 9/64", 5/32", 3/16", 7/32", 1/4" Drills and Lock-N-Load® Quick-Change	135°	Black Oxide	4935643
15-Piece Set	Titanium Coated HSS Fractional Straight Shank Jobber	1/16"-3/8"	135°	TiN	4935607
15-Piece Set	Titanium Turbomax	1/16" - 3/8"	TURBOMAX	TiN	3018009
18-Piece Set	Titanium Turbomax	1/16" - 1/2"	TURBOMAX	TiN	3018010
9-Piece Set	Titanium Turbomax & Unibit	1/16" - 3/8" Unibit #1 & #4	TURBOMAX	TiN	3018008
33-pc Set	Drill/Drive Set	3/8" X 6", 1/2" X 6", 5/8" X 6", 3/4" X 6", 7/8" X 6", 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, T15, T20, T25, #2 Phillips, #2 Square, T20, T25, 15/16", 15/16", 1/4"			1890206
43-pc Set	Drill/Drive Set	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 1/4"x2-1/4", #2 Phillips, #2 Square, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, T20, T25, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, 3 Square, T10, T15, T20, T25, T27, T30			1890223