

Pro Set Cases



314018



318015



316015



4935643



3018009

Description	Type	Contents	Point	Finish	Item #
15-Piece Set	Black Oxide HSS Fractional Straight Shank Jobber Length	1/16" - 3/8"	135°	Black Oxide	314015
18-Piece Set	Black Oxide HSS Fractional Jobber Length	1/16" - 1/2" with 3/8" Reduced Shank	135°	Black Oxide	314018
20-Piece Set	Drill/Drive Set with Black Oxide HSS Drills and Screwdriver Bits	1/16" (2), 3/32", 1/8" (2), 5/32", 3/16", 1/4" Drills and 12 Screwdriver and Nutdriver Bits	135°	Black Oxide	357020
15-Piece Set	Cobalt HSS Fractional Straight Shank Jobber Length	1/16" - 3/8"	135°	Cobalt	316015
15-Piece Set	TURBOMAX® HSS Fractional Straight Shank Jobber	Length 1/16"-3/8"	TURBOMAX	Black & Gold Oxide	318015
18-Piece Set	TURBOMAX HSS Fractional Jobber	Length 1/16"-1/2" with 3/8" Reduced Shank	TURBOMAX	Black & Gold Oxide	3018024SM
12-Piece Set	Black Oxide HSS 1/4" Hex Shank Jobber Length	1/16", 5/64", 3/32", 7/64", 1/8" (2), 9/64", 5/32", 3/16", 7/32", 1/4" Drills and Lock-N-Load® Quick-Change	135°	Black Oxide	4935643
15-Piece Set	Titanium Coated HSS Fractional Straight Shank Jobber	1/16"-3/8"	135°	TiN	4935607
15-Piece Set	Titanium Turbomax	1/16" - 3/8"	TURBOMAX	TiN	3018009
18-Piece Set	Titanium Turbomax	1/16" - 1/2"	TURBOMAX	TiN	3018010
9-Piece Set	Titanium Turbomax & Unibit	1/16" - 3/8" Unibit #1 & #4	TURBOMAX	TiN	3018008
33-pc Set	Drill/Drive Set	3/8" X 6", 1/2" X 6", 5/8" X 6", 3/4" X 6", 7/8" X 6", 1/16, 5/64, 3/32, 1/8, , 5/32, 3/16, 1/4, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, T15, T20, T25, #2 Phillips, #2 Square, T20, T25, 15/16", 15/16", 1/4"			1890206
43-pc Set	Drill/Drive Set	1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4, 1/4"x2-1/4", #2 Phillips, #2 Square, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, T20, T25, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, 3 Square, T10, T15, T20, T25, T27, T30			1890223